



Part Number : [1300480313](#)


Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Pigtail, 22 AWG, Green TPU WSOR Cable, 2.0m (6.56') Length

Series Number : 120108

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : E10A00612M020



Documents & Resources

Drawings

[1300480313_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120108
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Pigtail, 22 AWG, Green TPU WSOR Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	78172545786

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Cable Diameter	6.80mm (.268")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Green
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	166.900/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-40° to +80°C
Wire/Cable Type	Shielded TPE/AWM 21215
Wire Size (AWG)	22