



Main

Range of product	Harmony XVC6
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	2 illuminated units
Sound signalling	Without
Mounting diameter	60 mm
Component name	XVC
Light source	Red LED steady Orange LED steady
[Us] rated supply voltage	100...240 V
Supply circuit type	AC

Complementary

Material	PBT + ABS (UL94-V0) (top cover) ABS (acrylonitrile butadiene-styrene) (base unit) Polycarbonate (illuminated unit)
Product mounting	On base
Cable cross section	0.33 mm ² 0.83 mm ²
AWG gauge	18 22
Cable length	750 mm 850 mm
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	50 mA
Product weight	0.5 kg
Height	272 mm

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class I conforming to EN/IEC 61140
IP degree of protection	IP54 in flat surface installation conforming to EN/IEC 60529


Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b (mm)	b (in.)
1 stage	232	9.13
2 stages	272	10.71
3 stages	312	12.28
4 stages	352	13.86
5 stages	392	15.43

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

