

PU foam 2-in-1

Technical Data Sheet

Technical Data Sheet

Product name: PU foam 2-in-1
Sales code: 32516

Creation date: 27 Aug 2015

Version: 1.1
Replaces: 1.0

Section 1: General description

Mono component PU foam which expands and hardens with ambient humidity. Professional quality, convenient for all common used substrates in constructions.

The aerosol has a remarkable valve system that allows manual application as well as the use of an application gun.

Section 2: Features

- Appropriate for sealing, insulating, filling and fixing.
- Excellent adhesion to all common construction materials.
- The cured foam can be either covered with a filler-primer or straight painted.
- Manual application for the filling of cavities.
- The aerosol fits on an application gun for precise dosing application.
- Expands 2 to 3 times the applied volume.
- Excellent thermal and acoustic insulation properties.

Section 3: Applications

- Filling of all kind of cavities in a building construction.
- Insulation of conduits
- Thermal and acoustic insulations
- Fixation of building components.
- Production of scale-models.

Section 4: Directions

Manual use:

- Shake well.
- Click/turn the manual dispensing tube with trigger, on the valve: place the wings against the openings on the valve. While pushing slightly, turn a quarter turn. Press short to position the tube well on the valve.
- Humidify the surfaces to be treated slightly.

PU foam 2-in-1

Technical Data Sheet

- Hold the can upside down. Place a finger on the trigger, on each side of the dispensing tube and activate by pressing the trigger straight down on the can (do not tilt)
- Once activated, the can might be used in all positions.

Use with the application gun:

- Shake well.
- Screw the aerosol on the gun.
- Humidify the surfaces to be treated slightly.
- Regulate the flow rate with the throttling nut on the gun.
- After removal of an empty aerosol, clean the gun with CRC PU Foam Cleaner.

Note: Clean spoilage of non cured product immediately with CRC PU Foam Cleaner. Cured product only allows mechanical removal.

A safety data sheet (MSDS) according to EU directive 91/155/EEC and amendments is available for all CRC products.

Section 5: Typical product data (without propellant)

Color	: GreenFire reaction class	: B3	DIN 4102-1
Ambient application temperature	: -10°C to +35°C		
Maximal gap filling	: manual 60%		
	with application gun 80%		
Drying time	: to touch 10 min	FEICA TM 1014	
	to be cut 45 min	FEICA TM 1005	
Expanded volume	: a 500 ml aerosol produces	FEICA TM 1003	
	23 liters when applied manual		
	30 liters when applied with a gun		
Thermal conductivity	: 0,036 W/m.K	EN 12667	
Tensile strength	: applied manual : 107 kPa	ISO 527	
	applied by gun : 76 kPa		
Temperature resistance	: permanent -40°C to +90°C		
	temporarily -40°C to 130°C		
Conservation and storage	: At a temperature between 5°C and 25°C		
	Straight up, 18 months in the original closed packaging in a fresh and dry environment.		

Section 6: Packaging



PU foam 2-in-1

Technical Data Sheet

Aerosol 12x500 ML

All statements in this publication are based on service experience and/or laboratory testing. Because of the wide variety of equipment and conditions and the unpredictable human factors involved, we recommend that our products be tested on-the-job prior to use. All information is given in good faith but without warranty neither expressed nor implied. This Technical Data Sheet may already have been revised at this moment for reason such as legislation, availability of components and newly acquired experiences. The latest and only valid version of this Technical Data Sheet will be sent to you upon simple request or can be found on our website: www.crcind.com. We recommend you to register on this website for this product so you will be able to receive any future updated version automatically.