




RAST

TE Internal #: 3-1534799-3

Wire-to-Board, 13 Position, 2.5 mm [.098 in] Centerline, Insulation Displacement (IDC), 1 Row, Natural, PA 6 GF, Standard Edge Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**
Number of Positions: **13**
Centerline (Pitch): **2.5 mm [.098 in]**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**
Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	13
Number of Rows	1
Connector Contact Load Condition	Selectively Loaded
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	50 VAC, 250 VAC
-------------------	-----------------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features	
Contact Retention Within Housing	With
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Copper Tin
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Current Rating (Max)	2 A
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
PCB Mount Retention	Without
Contact Retention Type Within Housing	Locking Lance
Mating Retention	Without
Mating Alignment Type	Keyed
Mating Alignment	With
PCB Mount Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	PA 6 GF
Dimensions	
Card Slot Depth	5.05 mm
Compatible Insulation Diameter Range	1.2 – 1.4 mm[.047 – .055 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Connector Height	7.3 mm[.287 in]
Wire Size	24 – 22 AWG
Usage Conditions	
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
Operation/Application	
Circuit Application	Signal



Industry Standards

UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWEPT 750°C (Without Flame)

Packaging Features

Packaging Quantity	4312
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2406233-3
AMP DUOPLUG MK2 GWT V0 13P Sel

TE Part # 1-1534799-9
DUOPLUG MK II SELECTIVE LOADED

TE Part # 3-1534799-1
AMP DUOPLUG MK2 CONNECTOR 11P SELECTIVE

TE Part # 5-1534799-3
AMP DUOPLUG MARK II CONNec. SELEC.LOADED

TE Part # 2-1740918-3
AMP DUOPLUG2.5 MKII 3P W. PCB LOCK

TE Part # 1-1740918-3
AMP DUOPLUG2.5 MKII 3P W. PCB LOCK

TE Part # 2304528-3
AMP DUOPLUG MK2 CONNECTOR 13P SELECTIVE

TE Part # 4-1534799-3
AMP DUOPLUG MARK II CONNec. SELEC.LOADED

TE Part # 1-1740501-3
AMP DUOPLUG 2.5 MKII 3P W. PCB LOCK

Customers Also Bought

TE Part #1971600-1
POWER DBL LOCK CAP HSG 8P(GWT)

TE Part #280232-8
250 FASTON POST INS.,REC.,1 POS, NATRUAL

TE Part #690718-1
ANVIL-REVERSIBLE


TE Part #1-282002-4
MONO-SHAPE MK I CONN. ASSY TAB 2P

TE Part #179466-1
AMP POWER DBL LOCK CAP HSG 6P

TE Part #1534415-4
DUOPL POW FEM CON4P

TE Part #62016-2
187 FASTON REC 18-14 AWG TPBR

TE Part #63119-1
POSITIVE LOCK 250 REC 22-18 AWG TPBR



Documents

Product Drawings

AMP DUOPLUG MARK II CONNEC.SELEC.LOADED

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1534799-3_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1534799-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1534799-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English