

# Product information

## HP330DZW + TD090DZW



### DK1493WX

#### Models in Kit

DC10WA - 7.2V-10.8V BATTERY CHARGER  
HP330DZ - 10.8v LXT COMBI DRILL/DRIVER (**WHITE**)  
TD090DZW - 10.8V IMPACT DRIVER (**WHITE**)  
194550-6 - 10.8V Li-ion Battery (2x)



#### Technical specifications

##### 194550-6

Battery Ah 1.3 Ah  
Battery Type Li-ion  
Voltage 10.8 v  
Battery ID BL1013

##### DC10WA

Battery Range 7.2 - 10.8 v  
Battery Type Li-ion

##### HP330DZ

Battery Type Lithium-ion  
Battery Quantity (1.3Ah)2  
Charging Time 50 min  
Body only machine  
Voltage 10.8 v  
Capacity in Steel 10 mm  
Capacity in Wood 21 mm  
Chuck Capacity 10 mm  
Capacity in Masonry 8 mm  
Blows per Minute (Hi) - ipm 0 - 19500 ipm  
Blows per Minute (Lo) - ipm 0 - 5300 ipm  
No Load Speed (Hi) 0 - 1300 rpm  
No Load Speed (Lo) 0 - 350 rpm  
Max Torque S/H 14 / 30 Nm  
Torque Settings 18 + Drill Mode  
Vibration: Drilling 2.5 m/sec<sup>2</sup>  
Vibration K factor 1.5 m/sec<sup>2</sup>  
Net weight 1.1 kg

##### TD090DZW

Battery Type Lithium-ion  
Battery Quantity (1.3Ah)2  
Charging Time 50 min  
Voltage 10.8 v  
Impacts 0 - 3000 ipm  
Machine Screw Size M4-M8 mm  
Standard Bolt M5-M12  
High Tensile Bolt M5-M10  
Coarse thread (length) 22 - 90 mm  
Noise sound pressure 92 dB(A)  
Noise sound power 103 dB(A)  
Noise K factor 3 dB(A)  
No Load Speed 0 - 2400 rpm  
Max Torque 90 Nm  
Vibration: Fastening Bolt 10 m/sec<sup>2</sup>  
Vibration K factor 1.5 m/sec<sup>2</sup>  
Net weight 0.92 kg

## DK1493WX



### User benefits

#### 194550-6

- Features: Foam cell technology. Slide on battery - firm holding with multi contacts and shock absorbing pack, will not puncture and remains cool even in heavy use.
- Lightweight and shock-absorbing. The Li-ion range delivers 430% more working capacity during it's lifetime compared to Ni-Cad and is 40% Lighter than Ni-MH. The Li-ion has minimal depletion of power during use or in storage over it's lifetime.

#### HP330DZ

- 10mm (3/8") Single-sleeve keyless chuck
- With 2-speed gear selection
- Ergonomically designed handle with rubberized soft grip provides comfortable grip and more control while minimizing hand fatigue and pain.
- Single LED job light with pre-glow function
- Variable speed control by trigger
- Hammer drill mode has been added for drilling holes in mortar etc

#### TD090DZW

- Conveniently located push button for forward and reverse.
- High comfort grips.
- Ideal for applications in tight spaces.
- Keyless single sleeve hex chuck.
- LED job light.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Minimal pressure required from the operator.