



Fuse-link, medium voltage, 31.5 A, AC 22 kV, 51 x 565 mm, full-range, BS, with striker

24FDIHA31.5

General specifications		
Product name		Eaton Bussmann series medium voltage BS air fuse
Part no.		24FDIHA31.5
EAN		5027590468930
Product Length/Depth		565 millimetre
Product height		50.8 millimetre
Product width		50.8 millimetre
Product weight		2702 gram
Compliances		BS 2692-1
Product Tradename		None
Product Type		Medium voltage BS air fuse
Product Sub Type		None
Electrical data		
Amperage Rating		31.5 A
Voltage rating		24 kV
Breaking capacity		35.5 kA
Performance Cat According To IEC 60282-1		Full-range
Rated frequency - min		50 Hz
Class		Class full-range
Resistance		893 ohms
Product specifications		
Application		used in fuse switch combination units, fuse bases and fuse switches protection of primary side transformers
Fuse size		50.8 x 565 mm
Standard		British Standard
Mounting method		Clip-in
Compatible fuse clip		
Used with		A3354710 Fuse clip

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Medium/high voltage fuse (EC003507)		
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Medium-/high voltage fuse (ecl@ss13-27-14-19-11 [AGA534005])		
Rated current	A	31.5
Rated voltage	kV	24
Voltage type		AC
Rated frequency	Hz	50 - 50
Breaking capacity	kA	35.5
Utilization category		Other
Application		Primary side transformer protection
Length	mm	565
Diameter	mm	51
Performance category according to IEC 60282-1		Full-range
With striker		Yes
Standard		British Standard
Release characteristic		Other
Installation technique		Air

