


# HMC 461/463 GTP - Green Standard HMS 462/464 Water Tight NEMA 4

LENS OPTIONS



## NOTES:

Material: Lens - Polycarbonate U.L. Rating 94-V2 LED Connector - Polyester U.L. Rating 94-V0 Header Connector - Polyester U.L. Rating 94-V0

U.L. Manual - "Thermoplastic material used on a secondary circuit."

Wire: 1007/1569 - 24 AWG, stranded (105° C) Mounting: Lens - panel hole size 5/16" (8.0mm) Tested: UV, Solar, Shock, Vibration, Temperature -45° - 105°C. HMS 462/464 meet NEMA 4

# U.S. & FOREIGN PAT. ISSUED & PEND.


	REVISIONS				VICC D	/ N. II .	CNIV	100				N 16
	NO	DESCRIPTION	DATE	BY	VCC P/N: CNX 460 CABLE ASSEMBL							SLY
0	1	Add HMC 463, HMS 464	12/15/08	JG	TRE	R						
	2				VISUAL COMMUNICATIONS COMPANY, INC. 190 Bosstick Blvd, Ste. 101 San Marcos, California 92069 U.S.A. Phone (760) 560-1300 Fax (760) 560-1301 e-mail vccsales@vcclite.com							
	3											com
	4				TOLERANCES		SCALE	N/A	DATE	11/12/08	DRAMING NO.	REV.
	_			-	DECIMAL ±.5	500	DIAMETER		DRAWN BY	JDG	CNX 460 CABLE_Assy	1
	5				ANGLE		RADII		CHK'D			=






# CABLE ASSEMBLY FOR 5mm & 10mm LED LIGHTS

### CNX 440 STANDARD ASSEMBLIES (5mm)



LED 5mm bi-lead - trim lead length .250" ± .01" (5.58mm)
Panel Thickness - .032" to .125", Panel Hole: .312" (8.0mm)


Recommended LEDs - 5mm bi-lead, 5mm tri-lead (tri-color) and 5mm six-lead (RGB)



LED 5mm tri-lead - leads custom formed by VCC

Panel Thickness - .032" to .125" Panel Hole: .312" (8.0mm)

### CNX 460 STANDARD ASSEMBLIES (10mm)



LED 10mm bi-lead - trim lead length .300" ± .01" (8.13mm)
Panel Thickness - .032" to .187", Panel Hole: .562" (14.0mm)


Recommended LEDs


 10mm bi-lead, 10mm tri-lead (bi-color), 10mm six lead (RGB) and Hi-Flux four-lead ultra bright. HMC 461 (STANDARD) Hi-Flux LED Display Panel Lock washer Socket (4 leads)

LED Hi-Flux lead length: Install as is.

Panel thickness - .032" to .187" Panel Hole: .562" (14.0mm).

# **HEADER CONNECTORS AND HEADERS**





### **ORDERING CODES**

### CNX 440 CONNECTOR STYLE **TERMINATION** WIRE SIZE WIRE COLOR WIRE LENGTH X = STRIPPED END CNX 440 for 5mm LED STANDARD 4 INCHES - WHT - BLK E = SINGLE ROW 06 6 INCHES CNX 460 for 10mm LFD 4 24 AWG - RFD - BLK 6 - WHT - BLK - RED 8 INCHES D = DUAL ROW 80 See above for avaliable lens options 12 18 12 INCHES 0 - WHT - BLK - RED - GRN 02 = 2 Wires (Sold Separately) 18 INCHES 03 = 3 Wires 24 24 INCHES 04 = 4 Wires

ADDITIONAL OPTIONS AVAILABLE