

KERN 347-137-100

KERN

Supporting bar, OIML Class M1, 5 kg, stainless steel fine turned



Category

Brand	KERN
Product category	Individual weight
Product group	Supporting Bar
Product family	347

Measuring System

Test weight - nominal value	5 kg
Test weight - volume uncertainty (cm ³)	12,0465
Weight OIML class	M1
Test weight - volume (cm ³)	595,2381
Permissible tolerance according to OIML (+/-)	250 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600
Test weight - Density (kg/m ³)	8000
Test weight - Density uncertainty (kg/m ³)	100

Construction

Shape weight	Supporting bar (Type B)
Dimensions (Ø×H)	138×691,5 mm
Material	stainless steel fine turned
Max. total weight	95 kg
Max. single weight	10 kg
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-643
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	138×138×691,5 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	5,0 kg
Shipping weight	5 kg
Shipping volume weight	2,6 kg

Product information

GTIN/EAN number	4045761366817
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

