


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		Z1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D

C

B


A



- 1 2.54μm [.000100] MIN TIN OR TIN-LEAD OVER 1.27μm [.000050] MIN NICKEL.
- 2 PLATED WITH 0.76μm [.000030] GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, ALL OVER 1.27μm [.000050] NICKEL UNDERPLATE.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL 0.76μm [.000030] TOTAL ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, ALL OVER 1.27μm [.000050] NICKEL UNERPLATE.
- 3 GOLD PLATING PER MIL-G-45204.
TIN PLATING PER MIL-T-10727.
NICKEL PLATING PER QQ-N-290.
- 4 GOLD FLASH ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, ALL OVER 0.76μm [.000030] NICKEL UNDERPLATE.
- 5 GOLD FLASH FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, 2.54μm [.000100] MIN TIN PLATED WIRE BARRELS, ALL OVER 0.76μm [.000030] MIN NICKEL.
- 6 0.76μm [.000030] MIN GOLD FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, 2.54μm [.000100] MIN TIN PLATED WIRE BARRELS, ALL OVER 1.27μm [.000050] MIN NICKEL.

SUPERSEDED BY 205201-5	SMALL PACK	SEE DETAIL C	NO	2	2-205201-8
OBSELETE	STANDARD	-	YES	6	2-205201-5
SUPERSEDED BY 205201-6	STANDARD	-	YES	5	2-205201-2
SUPERSEDED BY 205201-6	STANDARD	-	YES	1	1-205201-4
	STANDARD	SEE DETAIL C	NO	4	205201-7
	STANDARD	-	YES	4	205201-6
	STANDARD	SEE DETAIL C	NO	2	205201-5
	STANDARD	-	YES	2	205201-3

PACKAGING TYPE	LOOSE PIECE	FOR MINI-APPLICATOR	FINISH 3	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 16 FEB 96	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 19 FEB 96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.FIX 19 FEB 96	NAME	
		PRODUCT SPEC		
MATERIAL COPPER ALLOY PER QQ-B-750		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		FINISH SEE TABLE		
		WEIGHT -	A2 00779 C=205201	
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1 REV Z1



DETAIL C