

TE Internal #: 3-173985-0
Board-In PCB Mount One-Piece IDC Connector, Vertical, Wire-to-Board, 10 Position, 2 mm [.079 in] Centerline, Discrete Wire, Through Hole - Press-Fit

[View on TE.com >](#)



Connectors > PCB Connectors > Board-In Connectors



PCB Connector Type: **PCB Mount One-Piece IDC Connector**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **10**
Centerline (Pitch): **2 mm [.079 in]**

Features

Product Type Features

PCB Connector Type	PCB Mount One-Piece IDC Connector
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	10
Compatible With Wire & Cable Type	Discrete Wire
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 VDC
-------------------	---------

Body Features

Primary Product Color	Light Blue
-----------------------	------------

Contact Features

Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	2 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Press-Fit



Mechanical Attachment

PCB Mount Retention Type	Retention Solder Tails
PCB Mount Alignment	Without
PCB Mount Retention	With

Housing Features

Centerline (Pitch)	2 mm [.079 in]
Housing Material	PBT GF

Dimensions

PCB Thickness (Recommended)	.8 mm [.031 – .063 in]
Connector Height	5.1 mm [.201 in]
Wire Size	28 – 26 AWG
Connector Length	22 mm [.866 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	130
Packaging Method	Box, Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

Solder Process Capability

Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58372-1
HEAD (IDC) 2MM C.T. W/O TL

TE Part # 353918-1
CT 1.5MM REC CONT CRIMP TYPE

TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME

TE Part # 3-173977-0
CT MT REC ASSY 10P BLUE

Customers Also Bought

TE Part #35665
TERMINAL,SOLIS R 8 5/8

TE Part #2-173983-4
AMP CT MT AMP-IN HDR-H YEL 4P

TE Part #320761
BUDGET RING 12-10 5/8

TE Part #2176339-1
CRGCQ 0603 10R 1%

TE Part #1622880-1
CRG0603 1% 200R

TE Part #5-2176451-1
CPF 0201 165R 0.1% 25ppm 1K RL

TE Part #747299-2
15 RCPT SP/FMS STD

TE Part #881545-2
SHUNT LP W/HANDLE 2 POS 30AU



Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_3-173985-0_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_3-173985-0_F.3d_igs.zip

English

Customer View Model

ENG_CVM_3-173985-0_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

MINI PRESS CT CONNECTOR (WAS IS-553J)

Japanese

Instruction Sheet (non U.S.)

Japanese