

Endress+Hauser FMU42-APB2A23A

Prosonic M FMU42



Level, ultrasonic, contactless. Application: liquids, solids.

Picture for reference only. Product appearance may vary based on configuration

Configuration of FMU42-APB2A23A:

Approval:	A	Non-hazardous area
Process Connection:	P	UNI flange 3"/DN80/80, PP max 2.5bar abs./ 36psia, suitable for NPS 3" Cl.150 / DN80 PN16 / 10K 80
Power Supply; Output:	B	2-wire; 4-20mA HART
Operation:	2	4-line display VU331, envelope curve display on site
Housing:	A	F12 Alu, coated, IP68 NEMA6P
Cable Entry:	2	Gland M20 (EEx d > thread M20)
Process Sealing Sensor / Flange:	3	EPDM
Additional Option:	A	Basic version

Alternative part number: FMU42-APB2A23A