




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **80**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Board-to-Board Configuration	Parallel
PCB Mount Orientation	Vertical
Number of Positions	80
Number of Rows	2

Electrical Characteristics

Operating Voltage	30 VAC
Insulation Resistance	5000 MΩ

Body Features

PCB Retention Feature Material	Copper Alloy
PCB Retention Feature Plating Material	Tin over Nickel
Primary Product Color	Black

Contact Features

Mating Pin Diameter	.46 mm[.018 in]
---------------------	-----------------



Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
	150 μin
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	.5 A

Termination Features

Rectangular Termination Post & Tail Width	.36 mm[.014 in]
Rectangular Termination Post & Tail Thickness	.08 mm[.003 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Alignment Type	Polarizing Tab
PCB Mount Retention Type	Hold-Down Post
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	LCP - GF (Liquid Crystal Polymer)
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Row-to-Row Spacing	1.27 mm[.05 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	4.75 mm[.187 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
---	-----------------------



UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity	9
Packaging Method	Box, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-147383-8
80 50/50 HDR SMT.390 W/HD VC

TE Part # 5-104693-8
80 50/50 HDR DRST SFMNT.390 SN

TE Part # 5-104656-8
80 50/50 HDR DRST SFMNT.320 SN

TE Part # 5-104655-9
80 50/50 HDR DRST SFMNT



TE Part # 5-104892-8
80 50/50 GRID RCPT W/LTCH LF

Also in the Series | AMPMODU 50/50 Grid

Board-to-Board Headers & Receptacles(193)

Connector Caps & Covers(7)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(193)

Rectangular Power Connectors(12)

Ribbon Cable Connectors(21)

Customers Also Bought

TE Part #3-794634-4
04P MICRO MNL ASSY,VRT,SMT LF

TE Part #5555165-5
M/J, LPF, R/A, 6P/2C, TIN, BULK PKG

TE Part #5520258-3
M/JTOP6P/6CPNL STOPSTRAY P

TE Part #284391-2
TERMI-BLOK PCB SIDE ENTRY STAC

TE Part #312479-000
202K132-100-0

TE Part #7955570001
TMS-SCE-1/8-2.0-S3-9

TE Part #5-147377-7
80 SYS50 SMT HDR DR SHD SN

TE Part #8-1474659-7
FSN-11.5A-3



Documents

Product Drawings

80 50/50 GRID DRST SFMNT RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-104652-8_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-104652-8_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-104652-8_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION1AND2

English

Ribbon Cable Interconnect Solutions

English

Fine Pitch Stacking Connectors - 1.27mm AMPMODU 50/50 Grid Connectors

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English