



Superior nitrile grip and a robust oil barrier. Cut resistant glove, level C.

**TEGERA® OIL GRIP 8857**



[Learn more](#)

**KNUCKLE AND TRIPLE-DIPPED FOR OILY ENVIRONMENTS**

This glove offers superior nitrile grip in oily environments that prevents slipping. Knuckle and triple-dipped with nitrile foam in the palm, gives a robust oil barrier. Cut resistant level C, re-enforcement between thumb and index finger. 18 gg knitted liner including CRF® cut resistant technology and contains 30% recycled polyester. Touchscreen functionality. Oeko-Tex approved. Withstands contact heat up to 100° C/212°F. Wide size range.

CHARACTERISTICS	FUNCTIONS
<ul style="list-style-type: none"> <li>• Durable</li> <li>• Good fingertip sensitivity</li> <li>• Flexible</li> <li>• Comfortable</li> <li>• Excellent grip in oily environments</li> </ul>	<ul style="list-style-type: none"> <li>• Withstands contact heat up to 100°C</li> <li>• For touchscreen</li> <li>• Reinforcement between index finger and thumb</li> <li>• Oil and grease resistant</li> </ul>



**PREVENTS RISK OF**

Cut injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping, contact with oil and fat

**PRIMARY ENVIRONMENTS OF USE**

Cut risk environments, moist environments, oily and greasy environments, dirty environments, harsh environments

**PRIMARY AREAS OF USE**

Agricultural work, assembly, building and construction, concrete work, engineering, glass industry work, machine operating, metalwork, mining, paper industry work, repair work, sheet-metal work, shop work, transport work, warehouse work

**PRIMARY INDUSTRIES OF USE**

Agriculture, mining, oil, gas, petrochemical, pulp and paper, glass, bricks, concrete, metal fabrication, machinery and equipment, mro, automotive, transportation, utilities, building and construction

**TYPE OF WORK**

Medium weight

**SPECIFICATION**

**TYPE** Cut resistant gloves, Heat protection gloves

**CATEGORY** Cat. II

**COLLECTION** Oil Grip

**LINING MATERIAL** 18 gg, CRF® Technology, Glass fibre thread, HPPE, Recycled polyester, Spandex, Stainless steel fibre yarn

**LENGTH** 210-270 mm

**DEXTERITY** 5

**GRIP DESIGN** Foam grip pattern

**COLOUR** Black, Blue, Red

**PAIRS PER: BUNDLE/CARTON** 6/72

**DISPLAY TYPE** Bulk pack

**DIPPING** 3/4 dipped, Triple-dipped

**DIPPING MATERIAL** Nitrile, Nitrile foam

**CUFF STYLE** Knitwrist cuff

**CUFF MATERIAL** Textile

**CUT RESISTANCE (EN ISO 13997)** Cut resistance level C

**CUT RESISTANCE (EN ISO 13997) TDM:** 11.6 N

**INNER MATERIAL SPECIFICATION** HPPE (High performance polyethylene), Recycled polyester, Stainless steel fibre yarn, Glass fibre thread, Elastane

**OUTER MATERIAL SPECIFICATION** Nitrile

**COMPLIANCE**



TP TC 019:2011



EN 407:2020 (No flame protection) X1XXXX



EN ISO 21420:2020



Contact heat rating valid for palm area only

Note: This product needs a few minutes of oil contact to activate the oil grip.

**FEATURES**



SIZE		ARTICLE NUMBER	EAN
6	XS	8857-6	7340118472744
7	S	8857-7	7340118472898
8	M	8857-8	7340118473048
9	L	8857-9	7340118473192
10	XL	8857-10	7340118473345
11	XXL	8857-11	7340118473499
12	3XL	8857-12	7340118473642

**ejendals**

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com