

VS-ST-LK-3,6/22,4/4,6 - D-SUB power contact



1688269

<https://www.phoenixcontact.com/gb/products/1688269>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power contacts, for D-SUB combination inserts, pin, solder cup, straight, rated current 40 A, gold-plated

Commercial data

Item number	1688269
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABNCAC
Product key	ABNCAC
Catalog page	Page 447 (C-2-2019)
GTIN	4017918179663
Weight per piece (including packing)	2.069 g
Weight per piece (excluding packing)	2.06 g
Customs tariff number	85366990
Country of origin	DE

VS-ST-LK-3,6/22,4/4,6 - D-SUB power contact



1688269

<https://www.phoenixcontact.com/gb/products/1688269>

Technical data

Notes

General	Power contacts must be ordered separately since they are not included in the scope of supply of the contact carriers.
---------	---

Product properties

Product type	Contacts
Type	Individual male contact
Contact material type	turned

Electrical properties

Maximum load current	40 A
Rated surge voltage	1 kV
Rated current	40 A (at 20 °C)
Insulation resistance	≥ 5 GΩ
Test voltage	1000 V

Connection data

Maximum load current	40 A
Connection method	Solder cup

Dimensions

Width	5.5 mm
Height	5.5 mm
Length	22.9 mm

Mechanical characteristics

Contact diameter	4.6 mm
------------------	--------

Material specifications

Material	Metal
Contact material	Copper alloy
Contact surface material	Au/Sn

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 7.00 N
Extraction force per signal contact	approx. 5 N

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 130 °C
---------------------------------	-------------------

VS-ST-LK-3,6/22,4/4,6 - D-SUB power contact



1688269

<https://www.phoenixcontact.com/gb/products/1688269>

Mounting

Mounting type	Solder connection
---------------	-------------------

VS-ST-LK-3,6/22,4/4,6 - D-SUB power contact



1688269

<https://www.phoenixcontact.com/gb/products/1688269>

Classifications

ECLASS

ECLASS-13.0	27440392
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

VS-ST-LK-3,6/22,4/4,6 - D-SUB power contact



1688269

<https://www.phoenixcontact.com/gb/products/1688269>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	486a16d0-0d02-4f6b-b90d-47726b15e33b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk