

# TIMKEN

The Timken Company  
 4500 Mt Pleasant St. NW  
 N. Canton, OH 44720  
 Phone: (234) 262-3000  
 E-Mail: [CustomerCAD@timken.com](mailto:CustomerCAD@timken.com) • Web site: [www.timken.com](http://www.timken.com)

## Timken Part Number 43125 - 43312, Tapered Roller Bearings - TS (Tapered Single) Imperial

This is the most basic and most widely used type of tapered roller bearing. It consists of two main separable parts: the cone (inner ring) assembly and the cup (outer ring). It is typically mounted in opposing pairs on a shaft.



[Specifications](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

### Specifications

<b>Series</b>	43000
<b>Cone Part Number</b>	43125
<b>Cup Part Number</b>	43312
<b>Design Units</b>	Imperial
<b>Bearing Weight</b>	0.600 Kg 1.30 lb
<b>Cage Type</b>	Stamped Steel

### Dimensions

<b>d - Bore</b>	31.750 mm 1.2500 in
<b>D - Cup Outer Diameter</b>	79.375 mm 3.1250 in

<b>B - Cone Width</b>	24.074 mm 0.9478 in
<b>C - Cup Width</b>	17.463 mm 0.6875 in
<b>T - Bearing Width</b>	25.400 mm 1.0000 in

#### Abutment and Fillet Dimensions

<b>R - Cone Backface "To Clear" Radius<sup>1</sup></b>	1.520 mm 0.06 in
<b>r - Cup Backface "To Clear" Radius<sup>2</sup></b>	1.52 mm 0.06 in
<b>da - Cone Frontface Backing Diameter</b>	41.40 mm 1.63 in
<b>db - Cone Backface Backing Diameter</b>	43.94 mm 1.73 in
<b>Da - Cup Frontface Backing Diameter</b>	74.68 mm 2.94 in
<b>Db - Cup Backface Backing Diameter</b>	67.06 mm 2.64 in
<b>Ab - Cage-Cone Frontface Clearance</b>	3.3 mm 0.13 in
<b>Aa - Cage-Cone Backface Clearance</b>	2.5 mm 0.1 in
<b>a - Effective Center Location<sup>3</sup></b>	-2.00 mm -0.08 in

#### Basic Load Ratings

<b>C90 - Dynamic Radial Rating (90 million revolutions)<sup>4</sup></b>	23900 N 5360 lbf
<b>C1 - Dynamic Radial Rating (1 million revolutions)<sup>5</sup></b>	92000 N 20700 lbf
<b>C0 - Static Radial Rating</b>	76200 N 17100 lbf
<b>C<sub>a90</sub> - Dynamic Thrust Rating (90 million revolutions)<sup>6</sup></b>	27300 N 6130 lbf

## Factors

<b>K - Factor<sup>7</sup></b>	0.87
<b>e - ISO Factor<sup>8</sup></b>	0.67
<b>Y - ISO Factor<sup>9</sup></b>	0.9
<b>G1 - Heat Generation Factor (Roller-Raceway)</b>	16.8
<b>G2 - Heat Generation Factor (Rib-Roller End)</b>	7.57
<b>Cg - Geometry Factor</b>	0.0774

<sup>1</sup> These maximum fillet radii will be cleared by the bearing corners.

<sup>2</sup> These maximum fillet radii will be cleared by the bearing corners.

<sup>3</sup> Negative value indicates effective center inside cone backface.

<sup>4</sup> Based on  $90 \times 10^6$  revolutions  $L_{10}$  life, for The Timken Company life calculation method.  $C_{90}$  and  $C_{a90}$  are radial and thrust values.


<sup>5</sup> Based on  $1 \times 10^6$  revolutions  $L_{10}$  life, for the ISO life calculation method.

<sup>6</sup> Based on  $90 \times 10^6$  revolutions  $L_{10}$  life, for The Timken Company life calculation method.  $C_{90}$  and  $C_{a90}$  are radial and thrust values for a single-row,  $C_{90(2)}$  is the two-row radial value.

<sup>7</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

<sup>8</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

<sup>9</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.



**IMPERIAL UNITS**

ISO Factor - e	0.67
ISO Factor - Y	0.9
Bearing Weight	1.3 lb
Number of Rollers Per Row	13
Effective Center Location	-0.08 inch

**TIMKEN**®

**43125 - 43312  
TS BEARING ASSEMBLY**

**THE TIMKEN COMPANY**  
NORTH CANTON, OHIO USA

K Factor	0.87
Dynamic Radial Rating - C90	23900 lbf
Dynamic Thrust Rating - Ca90	27300 lbf
Static Radial Rating - C0	76200 lbf
Dynamic Radial Rating - C1	92000 lbf

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

**FOR DISCUSSION ONLY**