



## Starrett KFC11032RS Fast Cut Bi-Metal Holesaw Kit (298-3216)



### Features

- 14 Pc Fast Cut Bi-Metal Holesaw Kit
- Holesaw Diameters: 16mm, 20mm, 22mm, 25mm, 32mm, 35mm, 38mm, 40mm, 51mm, 64mm, 76mm
- Arbors: A1 (14-30mm), A2 (32mm-210mm)
- Accessories: A5 Arbor Extension (Fits A2 Arbors)
- New tooth material with extra cobalt for enhanced heat and wear resistance - improving the product life.
- New 5.5 TPI positive rake tooth form provides less torque for a smoother, faster cut in all materials.
- 30% extra gullet volume for better material penetration.
- Ideal for stainless steel and mild steel sheet, tubes and other materials with a thickness of up to 3mm (1/8").
- 41mm (1.5/8") hole saw depth.

### Description

The new Fast Cut Bi-Metal Hole Saws contain an extra cobalt HSS tooth material for enhanced heat and wear resistance, along with a new 5.5 TPI positive rake tooth design, to ensure a smoother and faster cut when compared against our previous Constant Pitch Hole Saw. Specifically designed to cut stainless steel, metals and mild steel sheet, the Fast Cut Saws will also cut through wood, plastic, plaster and other materials. Recommended cutting depth - up to 3mm (1/8").