

3SBH1149A2

✓ ACTIVE

CII | CII 3SBH Relay


TE Internal #: 1-1617076-6

General Purpose Signal Relay, DC, Non-Polarized, Monostable, 4 Form C 4PDT-CO, 2 A Contact Rating, 12 VDC Coil Voltage, CII 3SBH Relay

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays > 4PDT Signal Relay: Electrically-Held, 1/5-Size Relay



Relay & Contactor Type: **General Purpose Signal Relay**

Current Type: **DC**

Coil Magnetic System: **Non-Polarized, Monostable**

Contact Arrangement: **4 Form C 4PDT-CO**

Contact Current Rating: **2 A**

[All 4PDT Signal Relay: Electrically-Held, 1/5-Size Relay \(24\)](#)

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay
------------------------	------------------------------

Configuration Features

Contact Arrangement	4 Form C 4PDT-CO
---------------------	------------------

Electrical Characteristics

Coil Resistance	115 Ω
Contact Current Rating	2 A
Coil Voltage Rating	12 VDC
Coil Power Rating DC	1.252 W

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------



Usage Conditions

Operating Temperature Range	-65 – 125 °C
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Operation/Application

Vibration Resistance	30G's, 10 – 3000Hz
Shock Resistance	75G's, 6ms
Current Type	DC
Coil Magnetic System	Non-Polarized, Monostable

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2-1617072-6
3SBC1517A2 = M39016/13-056M

Also in the Series | CII 3SBH Relay



PCB Relays(14)

Customers Also Bought



TE Part #1462042-8
IMC03GR=IM RELAY 140mW 5V 1CO



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #1996168-2
PIN HEADER



TE Part #1996168-1
3 ROW BOX P/H R/A CONT
REMOVED



TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS



TE Part #881545-2
SHUNT LP W/HANDLE 2 POS 30AU



TE Part #2000713-5
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #2332817-1
Vert RCPT Left End Half Multigig RT 3



TE Part #1-6450869-4
V/R 2ACP+1LP+32S+3HDP+1LP+1P



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec1_3SBH

English