

Eaton 185774

Catalog Number: 185774

Eaton DC1 Variable frequency drive, 230 V AC, 3-phase, 24 A, 5.5 kW, IP20/NEMA 0, Radio interference suppression filter, Brake chopper, FS3



General specifications

Product Name	Catalog Number
Eaton DC1 Variable frequency drive	185774
EAN	Product Length/Depth
4015081812738	175 mm
Product Height	Product Width
273 mm	129 mm
Product Weight	Certifications
6 kg	CE
	CSA-C22.2 No. 14
	IEC/EN61800-3
	IEC/EN 61800-3
	Certified by UL for use in Canada
	RoHS, ISO 9001
	Safety requirements: IEC/EN 61800-5-1
	UL 508C
	RCM
	UL
	UL Category Control No.: NMMS,
	NMMS7
	UL File No.: E172143
	EAC
	IEC/EN61800-5
	CUL
	Specification for general requirements:
	IEC/EN 61800-2
	UkrSEPRO
	UL report applies to both US and
	Canada

Features & Functions

Features

Parameterization: drivesConnect

Parameterization: drivesConnect mobile (App)

Parameterization: Fieldbus

Parameterization: Keypad

Fitted with:

Control unit

Breaking resistance

7-digital display assembly

Brake chopper

IGBT inverter

Radio interference suppression filter

Internal DC link

PC connection

Additional PCB protection

Functions

4-quadrant operation possible

General

Cable length

300 m, unscreened, with motor choke, maximum permissible, Motor feeder

$C3 \leq 25$ m, Radio interference level, maximum motor cable length

100 m, screened, maximum permissible, Motor feeder

200 m, screened, with motor choke, maximum permissible, Motor feeder

150 m, unscreened, maximum permissible, Motor feeder

$C2 \leq 5$ m, Radio interference level, maximum motor cable length

Communication interface

CANopen®, built in

OP-Bus (RS485), built in

Modbus RTU, built in

SmartWire-DT, optional

Connection to SmartWire-DT

Yes

In conjunction with DX-NET-SWD3 SmartWire DT module

Degree of protection

IP20

NEMA Other

Electromagnetic compatibility

1st and 2nd environments (according to EN 61800-3)

Frame size

FS3

Mounting position

Vertical

Product category

Variable frequency drives

Protection

Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)

Protocol

MODBUS

CAN

Other bus systems

EtherNet/IP

Radio interference class

C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.
Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments

Suitable for

Branch circuits, (UL/CSA)

Climatic environmental conditions

Altitude

Max. 4000 m

Above 1000 m with 1 % derating per 100 m

Ambient operating temperature - min

-10 °C

Ambient operating temperature - max

50 °C

Ambient operating temperature at 150% overload - min

-10 °C

Ambient operating temperature at 150% overload - max

50 °C

Ambient storage temperature - min

-40 °C

Ambient storage temperature - max

60 °C

Climatic proofing

< 95 average relative humidity (RH), no condensation, no corrosion

Main circuit

Heat dissipation capacity P_{diss}

0 W

Input current I_{LN} at 150% overload

26.4 A

Leakage current at ground I_{PE} - max

6.8 mA

Mains switch-on frequency

Maximum of one time every 30 seconds

Mains voltage - min

200 V

Mains voltage - max

240 V

Operating mode

U/f control

Sensorless vector control (SLV)

Speed control with slip compensation

Motor rating

Assigned motor current I_M at 110/120 V, 60 Hz, 150% overload

24 A

Assigned motor current I_M at 115 V, 50 Hz, 150% overload

24 A

Assigned motor current I_M at 220 - 240 V, 60 Hz, 150% overload

24 A

Assigned motor current I_M at 230 V, 50 Hz, 150% overload

24 A

Assigned motor current I_M at 400 V, 50 Hz, 150% overload

24 A

Assigned motor current I_M at 440 - 480 V, 60 Hz, 150% overload

24 A

Assigned motor power at 115/120 V, 60 Hz, 1-phase

7.5 HP

Assigned motor power at 230/240 V, 60 Hz, 1-phase

BLDC motors
PM motors
Synchronous reluctance motors

Output frequency - min

0 Hz

Output frequency - max

500 Hz

Output voltage (U2)

230 V AC, 3-phase

240 V AC, 3-phase

Overload current IL at 150% overload

36 A

Rated control supply voltage

10 V DC (Us, max. 10 mA)

Rated frequency - min

48 Hz

Rated frequency - max

62 Hz

Rated operational current (Ie)

24 A at 150% overload (at an operating frequency of 16 kHz and an ambient air temperature of +50 °C)

Rated operational voltage

240 V AC, 3-phase

230 V AC, 3-phase

Resolution

0.1 Hz (Frequency resolution, setpoint value)

Short-circuit protection rating

32 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring

Starting current - max

175 %, IH, max. starting current (High Overload), For 2.5 seconds every 600 seconds, Power section

Supply frequency

50/60 Hz

Switching frequency

8 kHz, 4 - 24 kHz adjustable (audible), fPWM, Power section, Main circuit

System configuration type

AC supply systems with earthed center point

7.5 HP

Assigned motor power at 460/480 V, 60 Hz

7.5 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

7.5 HP

Apparent power

Apparent power at 230 V

5.52 kVA

Apparent power at 240 V

5.76 kVA

Braking function

Braking resistance

20 Ω

Braking torque

Max. 100 % of rated operational current Ie, variable, DC - Main circuit

Switch-on threshold for the braking transistor

390 VDC

Control circuit

Number of inputs (analog)

2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)

Number of inputs (digital)

4 (parameterizable, 10 - 30 V DC)

Number of outputs (analog)

1

Number of outputs (digital)

1

Number of relay outputs

1 (parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))

Design verification

Equipment heat dissipation, current-dependent Pvid

Voltage rating - max

240 V

446 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

24 A

Static heat dissipation, non-current-dependent P_{vs}

0 W

Heat dissipation details

Operation (with 150 % overload)

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Application notes

[The OP System Bus - Parameterizing - Control](#)

[Conformal Coating](#)

[Dependency of the output current on switching frequency and ambient temperature](#)

[Motor data - Motor Protection - V/f curves Slip Compensation](#)

[Operating Single Phase Motors](#)

[PI controller](#)

[Set Point Setting](#)

[Connecting drives to generator supplies](#)

[Update DX-COM-STICK3](#)

[Fire Mode](#)

[Operating Permanent Magnet and Brushless DC Motors](#)

[Low Temperature Applications](#)

[I/O Configuration](#)

[Access to Parameter Levels 2 + 3 Parameter Lock - Load Default](#)

[DX-COM-STICK3_Connection](#)

[Starting, Stopping and Operation](#)

[How does the internal motor protection work?](#)

[Electromagnetic compatibility \(EMC\)](#)

Brochures

[eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf](#)

[DA-SW-drivesConnect](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

Declarations of conformity

[DA-DC-00003964.pdf](#)

[DA-DC-00004555.pdf](#)

[DA-DC-00004184.pdf](#)

[DA-DC-00004552.pdf](#)

Drawings

[eaton-frequency-inverter-dimensions-020.eps](#)

[eaton-frequency-inverter-3d-drawing-009.eps](#)

eCAD model

[DA-CE-ETN.DC1-32024FB-A20CE1](#)

Installation instructions

IL040024ZU

Installation videos

PowerXL Variable Frequency Drives DC1 and DA1 - EN

Video PowerXL DA1

Manuals and user guides

MN040059_EN

MN040018_EN

MN040003_EN

[eaton-canopen-communication-manual-for-variable-frequency-drives-variable-speed-starters-da1-dbl-dc1-de11-mn040019-en-us.pdf](#)

MN040022_EN

MN040023_EN

mCAD model

DA-CD-dc1_fs3

DA-CS-dc1_fs3

Multimedia

Looking for variable frequency drives DC1 and DA1 which can be used in harsh environments?

Product notifications

[eaton-drives-ecodesign-directive-mz040046en-en.pdf](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)