



## Main

Range of product	TeSys D
Product or component type	Mechanical latch block
Product compatibility	3 poles LC1D115 DC 3 poles LC1D80...D150 AC 3 poles LC1D80 DC 4 poles LC1D115 AC 4 poles LC1D115 DC 4 poles LC1D80 AC 4 poles LP1D80 DC
Control circuit voltage	256/277 V AC 50/60 Hz 256/277 V DC

## Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V IEC 60947-5-1 control circuit
Power required in VA	25 AC
Power required in W	30 W DC
Mechanical durability	500000 cycles
Operating rate	1200 cyc/h
On-load factor	10 %
Product weight	0,09 kg

## Environment

Product certifications	CSA UL
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C
RoHS EUR conformity date	0629
RoHS EUR status	Compliant

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.