



Power Triple Lock

TE Internal #: 4-1971875-7

Housing, Cap, Crimp, Wire-to-Wire, UL 94V-0, 15 Position, 6 mm [.236 in] Centerline, Power Triple Lock, Rectangular Wire & Cable Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Standard Temperature Caps | POWER TRIPLE LOCK



Connector Product Type: **Housing**
Connector & Housing Type: **Cap**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Wire**
Contact Retention Within Housing: **Without**

[All Standard Temperature Caps | POWER TRIPLE LOCK \(40\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Power Positions	15
Number of Positions	15
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

--	--



Connector & Keying Code	D
Cable Exit Angle	180°
Primary Product Color	Yellow

Contact Features

Contact Layout	Matrix
Contact Type	Tab
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	6 mm[.236 in]

Dimensions

Row-to-Row Spacing	8.1 mm[.319 in]
Panel Thickness (Recommended)	1 – 2 mm[.039 – .079 in]
Connector Height	31.15 mm

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2232356-5
PTL 3X5 CAP PANEL MT HOT WIRE
KEY A BLK



TE Part # 1452426-1
EXTRACTION TOOL



TE Part # 4-1971876-7
PTL 3X5 PLUG HSG STD TEMP KEY D
YEL



TE Part # CAT-P87074-T669
Locking Plate, POWER TRIPLE LOCK,
TPA






TE Part # CAT-P87074-T111
Tab Contact — POWER TRIPLE LOCK



TE Part # 1971789-1
CPA


Also in the Series | Power Triple Lock



Connector Contacts(26)




Connector Hardware(12)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(21)



Power Contacts(26)




Rectangular Power Connectors(301)



Wire-to-Board Headers & Receptacles (21)

Customers Also Bought




TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4



TE Part #1-1415543-5
RTE44110



TE Part #1614770-4
BDS 2 A 250 10R 10%



TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16



TE Part #ASA158F12390235000
623 PLUG



TE Part #ZPF000000000205388
CONTACT FEMALE CAL.20, M12 - FXP



TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP



TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS, CAL1,6



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1971875-7_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1971875-7_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1971875-7_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English