## KEMET Part Number: C1206C106K8PACTU

(C1206C106K8PAC7800)



## SMD Comm X5R, Ceramic, 10 uF, 10%, 10 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 1206



Dimensions		
L	3.2mm +/-0.2mm	
W	1.6mm +/-0.2mm	
Т	1.6mm +/-0.20mm	
В	0.5mm +/-0.25mm	

Packaging Specifications		
Packaging:	T&R, 180mm, Plastic Tape	
Packaging Quantity:	2000	

General Information	
Supplier:	KEMET
Series:	SMD Comm X5R
Style:	SMD Chip
Description:	SMD, MLCC, Temperature Stable, Class II
Features:	Temperature Stable, Class II
RoHS:	Yes
Termination:	Tin
Marking:	No
Miscellaneous:	Note: Referee time for X5R dielectric for this part number is 48 hours
Chip Size:	1206

Specifications		
Capacitance:	10 uF	
Capacitance Tolerance:	10%	
Voltage DC:	10 VDC	
Dielectric Withstanding Voltage:	25 VDC	
Temperature Range:	-55/+85C	
Temperature Coefficient:	X5R	
Dissipation Factor:	10.00% 1kHz 25C	
Aging Rate:	5% Loss/Decade Hour	
Insulation Resistance:	10 MOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

