




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**
Switch Contact Plating Material: **Gold Flash**
Case Color: **Black**
Case Material: **Polyphenylene Sulfide (PPS)**
Sealed Device: **No**

Features

Product Type Features

DIP & SIP Switch Type	DIP
Sealed Device	No
Actuator Style	Flush Actuator, Slide Actuator

Configuration Features

Number of Positions	2
Number of Switches	2
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	1 A
Operating Voltage	5 VDC

Body Features

Actuator Color	White
Product Orientation	Vertical
Case Color	Black



Case Material	Polyphenylene Sulfide (PPS)
Contact Features	
Contact Underplating Material	Nickel
	1.2 µin
PCB Contact Termination Area Plating Material	Gold
Switch Contact Plating Material	Gold Flash
Contact Base Material	Copper Alloy
Termination Features	
Termination Post & Tail Length	4 mm[.157 in]
Termination Method to PCB	Through Hole - Solder
Housing Features	
Centerline (Pitch)	2.54 mm[.1 in]
Dimensions	
Product Length	7.06 mm[.277 in]
Product Height	4 mm[.138 in]
Usage Conditions	
Operating Temperature Range	-30 – 85 °C
Operation/Application	
Assembly Process Feature	Auto-Insert Packaging
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Tube
Packaging Quantity	60
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2022 (223)
Does not contain REACH SVHC


Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 4-1825059-2
ADF08STTR04=DIP S,FLUSH,SMT-GW




TE Part # 5-1825059-4
ADF10STTR04=DIP S,FLUSH,SMT-GW



TE Part # 6-1825059-3
ADF06STR04



TE Part # 1-1825059-8
ADF04STTR04=DIP S,FLUSH,SMT-GW



TE Part # 1-1825059-3
ADF04S04=DIP SWT,FLUSH,SMT-GW

Also in the Series | Alcoswitch DIP




DIP & SIP Switches(66)



Rotary Switches(16)

Also in the Series | [Alcoswitch DIP ADF](#)



DIP & SIP Switches(66)

Customers Also Bought



TE Part #1734037-7
Champ 050 series,68pos,Au over PdNi




TE Part #1-796375-2
CPC PSTD RCPT,13-9,R/A LF



TE Part #6-1676123-7
1/2W SM M/OX 5% 470R



TE Part #1-213826-1
CPC 17-9 PSTD RECEPT ASSY LF



TE Part #1-282856-8
18P TERMI-BLOK PCB MOUNT



TE Part #213782-4
CPC RECPT ASSEMBLY SIZE 23-19



TE Part #2176308-9
RP 1E 0.1W 162K 0.1% 25PPM 5K RL



TE Part #9-2176307-1
RP 1E 0.1W 107K 0.1% 25PPM 5K RL



TE Part #9-2176307-3
RP 1E 0.1W 113K 0.1% 25PPM 5K RL



TE Part #776261-1
14POS,PIN DIA 1.3,HDR ASSY,
180DEG,COD 1



Documents

Product Drawings

ADF0204=DIP SWT,FLUSH,THRU/HL

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825002-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825002-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1825002-1_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

ADE_ADP_ADF_Datasheet

English