



FLAMESTAT STRETCH TROUSERS 2180 FSS

ART. NO: 300488

Softshell stretch material / Windproof and water repellent / Rib-knit stretch panels at waist / Concealed front button / Loop for id-card holder at waist / 2 front pockets / 2 back pockets with flaps and concealed snap fastening at outer edges / Double reinforced crotch seam / Large aramide-reinforced tool pocket / Large leg pocket with phone pocket, flap with velcro fastening / Pre-shaped knees / Aramide-reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / Adjustable leg length with 5 cm hem allowance / PFAS free / Metal free / Approved according to EN 61482-1-2 APC 2, EN 61482-1-1 ELIM: 23 cal/cm² EBT: 28 cal/cm², EN ISO 11612 A1 A2 B1 C2 F1, EN ISO 11611 A1 A2 class 2, EN 1149-5, EN 13034 Type PB [6], EN 14404 together with kneepads 124292 and EN 13758-2 UPF 40+ UV protection. Material approved UPF 500+ UV protection / Leasing-laundry tested according to ISO 15797 / OEKO-TEX® certified.

Material: Stretch material 47% modacrylic, 37% cotton, 12% polyurethane, 2% polyamide, 1% anti-static fibre, 1% elastane. Knee pockets 80% aramide, 2% anti-static fibre, 18% polyurethane. Inherent flame protection. PFAS free.

Weight: 365 g/m².

Color: F557 Dark navy/Neon Yellow

Size: Regular: C44-C62 Short: D84-D120



PRO

EN 11612 EN 11611 EN 1149-5 IEC 61482-2 EN 13034 EN 14404



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04