

Ball End L-Wrenches - ProGuard™ Finish

- Ball End inserts into screw at a 25° angle
- Ball End saves time by quickly funneling tool into screw
- 25° angle allows natural hand and wrist movement
- Superior Ball End strength and working angle
- Works in hard to reach places



Up to 20% stronger, with more torque and twice the wear resistance of standard grades of steel



Corrosion-resistant finish: Environmentally safe, provides better tool grip, resists solvents and is 5 times more corrosion resistant than competitor finishes

SIZE	INCH	MM	INCH	MM	PART#
LONG Metric Singles					
1.27	2.8	72	0.53	13	15749
1.5	3.0	77	0.53	14	15750
2.0	3.2	82	0.61	16	15752
2.5	3.5	88	0.69	17	15754
3.0	3.9	98	0.75	19	15756
3.5	3.9	100	0.85	21	15758
4.0	4.3	110	0.87	22	15760
4.5	4.5	114	1.00	25	15762
5.0	4.7	119	1.06	27	15764
5.5	4.9	124	1.14	29	15766
6	5.5	139	1.22	31	15768
7	5.5	140	1.30	33	15770
8	6.0	152	1.38	35	15772
9	6.2	159	1.46	37	15774
10	6.7	171	1.54	39	15776
11	7.9	200	1.63	42	15778
12	8.7	220	1.73	44	15780
13	9.4	240	1.88	48	15782
14	10.2	260	2.15	55	15784
17	11.0	280	2.42	61	15786
19	11.6	295	2.70	69	15788
22	13.0	330	3.07	78	10991
24	14.5	370	3.47	88	10993

SIZE	INCH	MM	INCH	MM	PART#
LONG Inch Singles					
.050	2.8	72	0.53	13	15702
1/16	3.0	76	0.56	14	15703
5/64	3.2	81	0.61	15	15704
3/32	3.4	86	0.65	16	15705
7/64	3.6	90	0.70	18	15706
1/8	3.8	95	0.75	19	15707
9/64	4.0	101	0.80	20	15708
5/32	4.2	107	0.84	21	15709
3/16	4.5	114	0.94	24	15710
7/32	4.9	124	1.03	26	15711
1/4	5.6	141	1.13	29	15712
5/16	6.0	152	1.25	32	15713
3/8	6.8	171	1.38	35	15714
7/16	7.5	191	1.50	38	15715
1/2	7.8	198	1.63	41	15716
9/16	9.0	229	1.75	44	15717
5/8	9.8	248	1.88	48	15718
3/4	11.3	286	2.13	54	15719
7/8	12.8	325	2.37	60	10920
1	14.2	362	2.62	67	10921