

FEATURES

- Auto-restart
- Smooth and highefficiency airflow
- Brushless DC
- Polarity protected

RS PRO, 12 V dc, DC Axial Fan, 40 x 40 x 20mm, 13.6m³/h, 1W

RS Stock No.: 541-4909



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS PRO, this high-performance ball bearing axial fan offers a cost-effective cooling solution without sacrificing on quality or reliability. With a robust plastic frame and impeller, the fan is perfect for lightweight applications where ventilation and cooling are required. The fan has a brushless DC motor which reduces the chance of overheating while delivering a high-speed high-pressure output.

General Specifications

Air Flow	13.6m^3/h				
Fan Speed	6900rpm				
Noise Level	28.5dB				
Direction of Curve	Backwards				
Frame	PBT, ULV94-0 Thermoplastic				
Impeller	PBT, ULV94-0 Thermoplastic				
Alarm Function	Yes				
Special Features	Tachometer				
IP Rating	IP44				
Applications	Server racks, Electrical cabinets and enclosures; Production Lines, Ceiling fan/ventilation Desktop computers, Motor engines (radiator in a car), Generators, Air compressors				

Electrical Specifications

Motor	Brushless DC, locked rotor protected, Auto Restart, Polarity Protected		
AC or DC Operation	DC		
Power Consumption	1W		
Supply Voltage	12VDC		
Maximum Current	80mA		



Insulation Resistance	Min.10M ohm at 500VDC
Insulation Resistance	Min.10M ohm at 500VDC

Mechanical Specifications

Dimensions	40mm x40mm x20mm		
Height	40mm		
Width	40mm		
Depth	20mm		
Bearing Type	Ball		
Life Expectancy	60,000 hours (L10)		

Operation Environment Specifications


Operating Temperature	-10°C to 70°C
Operating reinperature	-10 0 10 70 0

Approvals

Compliance/Certifications	UL, cUL, TUV, CE, UL94-V0

Dimensions: (mm)







RS Part No.	Speed	Airflow	Noise	Volts	Voltage	Current	Connection Type
5414915	7800	9	32	12	7~14	0.10	Wire
5414909	6900	7.8	28.5	12	7~15	0.08	Wire
5414892	6200	7	25	12	7~16	0.07	Wire
5415160	7800	9	32	24	10~27	0.09	Wire
5415154	6900	7.8	28.5	24	10~27	0.07	Wire
5415148	6200	7	25	24	10~27	0.06	Wire