



Image may differ from product. See technical specification for details.

LS 4565

LS universal washer for cylindrical and needle roller thrust bearings

Universal washers for cylindrical and needle roller thrust bearings are supplied as separate components. They are made of hardened carbon chromium bearing steel and their raceway surface is ground, while all other surfaces are turned. The washers are suitable for applications where accurate centring of the washers is not necessary or where low speeds are involved. They can be used as shaft or housing washers for AXK series bearings, and as shaft washers for AXW series bearings.

- Enable full interchangeability of washers
- Suitable where accurate centring of washers is not necessary
- Suitable for low-speed applications
- Available for cylindrical roller thrust bearings in the K 811 series

Overview

Dimensions

Bore diameter	45 mm
Outside diameter	65 mm
Height	4 mm


Properties

Bearing part	Universal washer
Material	Bearing steel
Coating	Without

Logistics

Product net weight	0.05 kg
eClass code	23-05-09-03
UNSPSC code	31171512

Technical specification



Dimensions

d	45 mm	Bore diameter universal washer LS series
D	65 mm	Outside diameter universal washer LS series
B	4 mm	Thickness universal washer LS series
r ₁	min. 0.6 mm	Chamfer dimension universal washer LS series

Tolerances and clearances

GENERAL BEARING SPECIFICATIONS

- Tolerances: table, values

DESIGN CONSIDERATIONS

- table

BEARING INTERFACES

- [Seat tolerances for standard conditions](#)



More Information

 Product details Designs and variants General bearing specifications Loads Temperature limits Permissible speed Design considerations Designation system	 Engineering information Principles of rolling bearing selection General bearing knowledge Bearing selection process Bearing failure and how to prevent it	 Tools SimPro Quick SKF Product select Bearing Frequency Calculator LubeSelect for SKF greases Heater selection tool
---	---	---



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.