

HC-M-02-CT-M-35 - Contact insert module



1684766

<https://www.phoenixcontact.com/gb/products/1684766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 2, power contacts: 2, control contacts: 0, Pin, Crimp connection, 1000 V, 100 A, 10 mm² ... 35 mm², application: Power, without crimp contacts

Commercial data

Item number	1684766
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7ACE
Product key	AF7ACE
GTIN	4067923240780
Weight per piece (including packing)	23.22 g
Weight per piece (excluding packing)	23.22 g
Country of origin	DE

HC-M-02-CT-M-35 - Contact insert module



1684766

<https://www.phoenixcontact.com/gb/products/1684766>

Technical data

Notes

General	Order crimp contacts separately
General	Order crimp contacts separately

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-02
Application	Power
Number of positions	2
Connection profile	2
Number of module slots	2
No. of power contacts	2
No. of control contacts	0
Contact material type	turned

Connection data

Connection technology

Connection technology	Crimp connection
-----------------------	------------------

Conductor connection

Conductor cross section	10 mm ² ... 35 mm ² (The cross section specification refers to the geometric cross section of the cable used)
Connection cross section AWG	8 ... 2 (The cross section specification refers to the geometric cross section of the cable used)

Dimensions

Width	34 mm
Height	52.3 mm
Length	29.5 mm

Electrical properties

Rated voltage (III/3)	1000 V
Rated surge voltage (III/2)	8 kV
Rated surge voltage (III/3)	8 kV
Rated current	100 A

Mechanical properties

Mechanical data

HC-M-02-CT-M-35 - Contact insert module



1684766

<https://www.phoenixcontact.com/gb/products/1684766>

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Drawings

Diagram



Derating diagram

HC-M-02-CT-M-35 - Contact insert module



1684766

<https://www.phoenixcontact.com/gb/products/1684766>

Classifications

ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

ETIM

ETIM 9.0	EC000438
----------	----------

HC-M-02-CT-M-35 - Contact insert module



1684766

<https://www.phoenixcontact.com/gb/products/1684766>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk