



 PRODUCT-DETAILS

OT200U30

OT200U30 SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT200U30
Product ID	1SCA022723R0570
EAN	6417019232676
Catalog Description	OT200U30 SWITCH-DISCONNECTOR
Long Description	Handle and shaft must be ordered separately.

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301117M0201
Environmental Information	1SCC301265D0201
Environmental Product Declaration - EPD	1SCC301282D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301031M0220
Mechanical Drawings	1SCC301684F0001 1SCC301683F0001 OT200-250U30.stp OT200-250U30
Environmental Product Declaration - EPD	1SCC301282D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301265D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	169.5 mm
Product Net Height	170 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	1.3 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	190 mm 7.5 in
Package Level 1 Depth / Length	290 mm 11.4 in
Package Level 1 Height	110 mm 4.3 in
Package Level 1 Gross Weight	1.5 kg 3.2 lb

Package Level 1 EAN

6417019232676

Technical

Conventional Thermal Current (I_{the})	Fully Enclosed 200 A
Degree of Protection	Front IP00
Distance Between Phases	Standard
Handle Type	Handle and shaft not included
Mechanical Durability	20000
Mounting Type	Base mounting
Number of Poles	3P
Operating Mode	Front
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 110 kW (500 V) 132 kW (690 V) 200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 30 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 8 kA
Special Functions	No
Standards	IEC 60947-3 / UL 98 / CSA C22.2 NO.4
Switches Operating Mechanism	Mechanism at the End of the Switch 30 (Right Side)
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 22.6 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Ampere Rating	200 A
Horsepower Rating UL/CSA	(acc. to UL 200 V) 60 Hp (acc. to UL 208 V) 60 Hp (acc. to UL 240 V) 75 Hp (acc. to UL 480 V) 150 Hp (acc. to UL 600 V) 200 Hp
Tightening Torque	acc. IEC 60947-1 22.6 N·m

Certificates and Declarations

© 2025 ABB. All rights reserved.

2025/10/08

Subject to change without notice

Declaration of
Conformity - CE

1SCC301131D2705

UL Certificate

cULus certificate OT200-400

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5290 >> Disconnect switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

