




TE Internal #: 1-2273126-4
M12 Cable Assembly, 4 Position, 1.5 m, Sensor/Actuator, A Code,
M12 Socket End A, M12 Plug End B, Double Ended, Plastic
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Male Straight to Female LED Double Ended Cable



Cable Assembly Type: **M12**
Number of Positions: **4**
Cable Assembly Length: **1.5 m**
M8/M12 Application Type: **Sensor/Actuator**
Connector & Keying Code: **A**

[All M12 A-Code Male Straight to Female LED Double Ended Cable \(60\)](#)

Features

Product Type Features

Cable Assembly Type	M12
Cable Assembly (End A)	M12 Socket
Cable Assembly (End B)	M12 Plug

Configuration Features

Number of Positions	4
---------------------	---

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------

Body Features

Jacket Material	PVC
Connector Color (End B)	Black
Connector Color (End A)	Black
Cable Color	Black
Wire Color (Base)	Brown, White, Blue, Black



Connector & Keying Code	A
-------------------------	---

Contact Features

Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Thread Size	M12 x M12
Connector Orientation (End A)	Right Angle
Connector Orientation (End B)	Straight

Housing Features

Housing Material	Plastic
------------------	---------

Dimensions

Outside Cable Diameter	5 mm[.196 in]
Wire Size	22 AWG

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Indicator Type	LED
M8/M12 Application Type	Sensor/Actuator
Shielded	No

Packaging Features

Packaging Method	Box
Packaging Quantity	25

Other

Field Serviceable	Yes
Cable Assembly Length	1.5 m
Cable Assembly Configuration	Double Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2022
(223)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T4151310004-003
RPC-M12-FS-4CON-PVC-1.5

Customers Also Bought



TE Part #4-1393249-0
W58-XC4C12A-10=W58



TE Part #4-1393249-6
W58-XC4C12A-30=W58



TE Part #T1410242000-000
H24B-AG



TE Part #K1156868
Battery Disconnecter 35-314-131-R-900



TE Part #2273002-1
M8 x 1.0 straight plug Pigtail




TE Part #T2111172201-000
HMN-017-F



TE Part #1546307-2
2P .374" DR BARRIER,W/WASHER



TE Part #TRAB24-49003P
OMNI,Ph,2400/4900MHz BK,3 dBi, 60W,



TE Part #T2070244001-000
H24BN-T6



TE Part #T2113000201-000
HMN-RJ45-F

Documents

Product Drawings

M12 angl d sckt to M12 strght plg 3 LED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2273126-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2273126-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2273126-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8 / M12 Connector System Catalog

Japanese

Product Specifications

Product Specification

English

1-2273126-4

M12 Cable Assembly, 4 Position, 1.5 m, Sensor/Actuator, A Code, M12 Socket End A,
M12 Plug End B, Double Ended, Plastic

