




Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories > LEAVYSEAL MOUNTING ACCESSORIES



Automotive Connector Accessory Type: **Alignment Plate**

Connector System: **Wire-to-Wire**

Primary Product Material: **PBT GF**

Primary Product Color: **Black**

Number of Positions: **39, 62**

All LEAVYSEAL MOUNTING ACCESSORIES (8)

Features

Product Type Features

Automotive Connector Accessory Type	Alignment Plate
Connector System	Wire-to-Wire

Configuration Features

Number of Positions	39, 62
---------------------	--------

Body Features

Primary Product Material	PBT GF
Primary Product Color	Black

Usage Conditions

Compatible With Connector Style	Housing For Male Terminals
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------



Packaging Features

Packaging Quantity	32
Packaging Method	Bag

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-L489-CH8172
LEAVYSEAL HOUSINGS



TE Part # 2098819-2
BLIND CONNECTOR,TAB HSG ASSY,
LEAVYSEAL

Also in the Series | LEAVYSEAL



Automotive Connector Caps & Covers
(16)




Automotive Housings(64)



Insertion & Extraction Tools(5)



Other Automotive Connector
Accessories(15)




PCB Headers & Receptacles(13)

Customers Also Bought



TE Part #1-967622-6
TIMER, CONNECTOR HOUSING



TE Part #964732-1
BEFESTIGUNGSSCHALE




TE Part #1-968968-3
2,5MM BU-GEH ASSY2P



TE Part #2098891-2
4 bay mounting frame assembly



TE Part #K1131877
Battery Disconnecter 35-210-141-R



TE Part #175063-1
040 MULTILOCK TAB CONT. L/P



TE Part #100284-1
2P.4MM SOCK.ASS.M27



TE Part #826883-2
02P ECONOSEAL "E"



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1813123-2_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1813123-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1813123-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

German