one-way flow control valve GRLA-3/8-QS-8-D Part number: 193150 * Core product range



Data sheet

Feature	Value
Valve function	One-way flow control function for exhaust air
Pneumatic connection, port 1	QS-8
Pneumatic connection, port 2	G3/8
Adjusting element	Slotted head screw
Mounting type	Threaded
Standard nominal flow rate in flow control direction	820 l/min
Standard nominal flow rate in non-return direction	450 850 l/min
Ambient temperature	-10 60 °C
Assembly position	Any
Operating pressure complete temperature range	0.2 10 bar
Standard flow rate in direction of flow control: 6 -> 0 bar	1,300 l/min
Standard flow rate in blocked direction: 6 -> 0 bar	1080 1420 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Medium temperature	-10 60 °C
Maritime classification	see certificate
Nominal tightening torque	10 Nm
Tolerance for nominal tightening torque	± 10 %
Product weight	60 g
Material of threaded plug	Wrought Aluminium alloy
Materials note	Conforms to RoHS
Material seals	NBR
Material release ring	POM
Material adjusting screw	Brass
Material swivel fitting	Zinc die-casting
	Chromed



FESTO