



Switches > Rocker Switches



Switch Type: **High Power Rocker Switch**
Product Mount Type: **Panel Mount**
Indicator/Imprint Legend: **-- O =**
Panel Cutout Size: **21.2 x 37 mm [1.002 x 1.086 in]**
Switch Contact Plating Material: **Silver**

Features

Product Type Features

Switch Type	High Power Rocker Switch
Actuator Type	Top
Actuator Style	Rocker
Switch Connection Type	Quick Connect Terminal

Configuration Features

Indicator/Imprint Legend	-- O =
Panel Cutout Size	21.2 x 37 mm[1.002 x 1.086 in]
Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On Off On

Electrical Characteristics

Power Rating	.33 hp
Contact Current Rating	16 A
Operating Voltage Range	125 VAC

Body Features

--	--

Product Orientation	Vertical
Actuator Color	Black

Contact Features

Terminal Tab Width	6.35 mm[.24 in]
Switch Contact Plating Material	Silver

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	No
----------------	----

Industry Standards

Compatible With Agency/Standards Products	VDE
Compatible With Approved Standards Products	UL E46765

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: DEC 2014 (161) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished


PRDDD3-16F-BB0GW

High Power Rocker Switch, Panel Mount, 21.2 x 37 mm [1.002 x 1.086 in] Panel Cutout, Silver Contact Plating




product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts




TE Part # 1571103-3
PRDDA1-16F-BB0CW,POWER
ROCKER




TE Part # 1571113-1
PRDDD1-16F-BB000,POWER ROCKER



TE Part # 1571113-2
PRDDD1-16F-BB0DW,POWER
ROCKER




TE Part # 1571103-5
PRDDA1-16F-BB0HW,POWER
ROCKER




TE Part # 1571103-1
PRDDA1-16F-BB000,POWER ROCKER


Customers Also Bought




TE Part #2-87175-5
12 LOCKING CLIP HSG SR MRKD




TE Part #787190-1
20 50SR R/A RCPT ASSY,REDESIGN




TE Part #3-640605-2
02P MTA156 CONN ASSY 20AWG LF




TE Part #4-640621-1
11P MTA100 CONN ASSY F/T NATL




TE Part #1986722-8
STR PLUG SPRING TYPE LH 8P, 3.81
mm



TE Part #1-2176379-4
RQ 0805 147R 0.1% 10PPM 5K RL



TE Part #3-2106489-3
Connector, Thru Hole-IDC, 3 pos,
24AWG



TE Part #9-1437471-6
SSC22AGA=120V 50/60HZ 10/300 S



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_1571113-6_E.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1571113-6_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571113-6_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English