## SIEMENS

## Data sheet

## 3RW3028-1BB14





SIRIUS soft starter S0 38 A, 18.5 kW/400 V, 40  $^\circ\text{C}$  200-480 V AC, 110-230 V AC/DC Screw terminals

General technical data		
product brand name		SIRIUS
product feature		
integrated bypass contact system		Yes
• thyristors		Yes
product function		
intrinsic device protection		No
motor overload protection		No
evaluation of thermistor motor protection		No
external reset		No
<ul> <li>adjustable current limitation</li> </ul>		No
inside-delta circuit		No
product component motor brake output	-	No
insulation voltage rated value	V	600
degree of pollution		3, acc. to IEC 60947-4-2
reference code according to EN 61346-2		Q
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750		G
Power Electronics		
product designation		Soft starter
operational current		
• at 40 °C rated value	А	38
• at 50 °C rated value	А	34
• at 60 °C rated value	А	31
yielded mechanical performance for 3-phase motors		
• at 230 V		
— at standard circuit at 40 °C rated value	kW	11
• at 400 V		
- at standard circuit at 40 °C rated value	kW	18.5
yielded mechanical performance [hp] for 3-phase AC motor at 200/208 V at standard circuit at 50 °C rated value	hp	10
operating frequency rated value	Hz	50 60
relative negative tolerance of the operating frequency	%	-10
relative positive tolerance of the operating frequency	%	10
operating voltage at standard circuit rated value	V	200 480
relative negative tolerance of the operating voltage at standard circuit	%	-15
relative positive tolerance of the operating voltage at standard circuit	%	10
minimum load [%]	%	10
continuous operating current [% of le] at 40 °C	%	115

power loss [W] at operational current at 40 °C during	W	19
operation typical		
Control circuit/ Control		
type of voltage of the control supply voltage		AC/DC
control supply voltage frequency 1 rated value	Hz	50
control supply voltage frequency 2 rated value	Hz	60
relative negative tolerance of the control supply voltage frequency	%	-10
relative positive tolerance of the control supply voltage frequency	%	10
control supply voltage 1 at AC at 50 Hz	V	110 230
control supply voltage 1 at AC at 60 Hz	V	110 230
relative negative tolerance of the control supply voltage at AC at 50 Hz	%	-15
relative positive tolerance of the control supply voltage at AC at 50 Hz	%	10
relative negative tolerance of the control supply voltage at AC at 60 Hz	%	-15
relative positive tolerance of the control supply voltage at AC at 60 Hz	%	10
control supply voltage 1 at DC	V	110 230
relative negative tolerance of the control supply voltage at DC	%	-15
relative positive tolerance of the control supply voltage at DC	%	10
display version for fault signal		red
Mechanical data		
size of engine control device		SO
width	mm	45
height	mm	125
depth	mm	150
fastening method		screw and snap-on mounting
mounting position		With vertical mounting surface +/-10° rotatable, with vertical mounting surface +/- 10° tiltable to the front and back
required spacing with side-by-side mounting		
• upwards	mm	60
• at the side	mm	15
downwards	mm	40
wire length maximum	m	300
number of poles for main current circuit		3
Connections/ Terminals		
type of electrical connection		
for main current circuit		screw-type terminals
for auxiliary and control circuit  number of NC contacts for auxiliary contacts		screw-type terminals 0
number of NC contacts for auxiliary contacts		1
number of CO contacts for auxiliary contacts		0
type of connectable conductor cross-sections for main contacts for box terminal using the front clamping point		
• solid		2x (1 2.5 mm²), 2x (2.5 6 mm²)
• finely stranded with core end processing		2x (1 2.5 mm²), 2x (2.5 6 mm²)
type of connectable conductor cross-sections for AWG cables for main contacts for box terminal		
<ul> <li>using the front clamping point</li> </ul>		1x 8, 2x (16 10)
type of connectable conductor cross-sections for auxiliary contacts		
• solid		2x (0.5 2.5 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>		2x (0.5 1.5 mm²)
type of connectable conductor cross-sections for AWG cables		
<ul> <li>for auxiliary contacts</li> </ul>		2x (20 14)
<ul> <li>for auxiliary contacts finely stranded with core end processing</li> </ul>		2x (20 16)
Ambient conditions		
installation altitude at height above sea level	m	5 000

environmental category	°C	<ul> <li>2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)</li> <li>1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4</li> <li>3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6</li> </ul>
during storage according to IEC 60721     during operation according to IEC 60721  mbient temperature     during operation     during storage lerating temperature		1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4 3K6 (no formation of ice, no condensation), 3C3 (no salt mist),
during operation according to IEC 60721      mbient temperature     during operation     during storage  lerating temperature		<ul><li>(sand must not get inside the devices), 1M4</li><li>3K6 (no formation of ice, no condensation), 3C3 (no salt mist),</li></ul>
during operation     during storage lerating temperature		
during storage lerating temperature		
lerating temperature		-25 +60
	°C	-40 +80
	°C	40
protection class IP on the front according to IEC 60529		IP20
ouch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front
rtificates/ approvals		
General Product Approval		EMC
Declaration of Conformity Test Certificates	s othe	er
CE UK ates/Test Repo		Confirmation Miscellaneous
/CSA ratings rielded mechanical performance [hp] for 3-phase AC motor		
• at 220/230 V		
— at standard circuit at 50 °C rated value	hp	10
• at 460/480 V		
— at standard circuit at 50 °C rated value	hp	25
contact rating of auxiliary contacts according to UL		B300 / R300
rther information		
iemens has decided to exit the Russian market (see here).		
https://press.siemens.com/global/en/pressrelease/siemens-wind-dow Siemens is working on the renewal of the current EAC certificate Please contact your local Siemens office on the status of validity of the EAC relevant market (other than the sanctioned EAEU member state Simulation Tool for Soft Starters (STS) https://support.industry.siemens.com/cs/ww/en/view/101494917	t <b>es.</b> he EAC certi	ification if you intend to import or offer to supply these products to a
nformation on the packaging <u>https://support.industry.siemens.com/cs/ww/en/view/109813875</u> nformation- and Downloadcenter (Catalogs, Brochures,) <u>thrs.//www.siemens.com/cs/</u>		
<u>https://www.siemens.com/ic10</u> ndustry Mall (Online ordering system) https://mall.industa.ciamaga.com/mall/ap/op/Catalog/product2m/th=2		
<pre>https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3 Cax online generator</pre>	<u>3RVV3U28-1E</u>	<u>2014</u>
http://support.automation.siemens.com/WW/CAXorder/default.aspx? Service&Support (Manuals, Certificates, Characteristics, FAQs,.	-	fb=3RW3028-1BB14
https://support.industry.siemens.com/cs/ww/en/ps/3RW3028-1BB14 mage database (product images, 2D dimension drawings, 3D m		ce circuit diagrams EPI AN macros
ttp://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW3		





last modified:

8/24/2023 🖸