

Desk Mount Dual Monitor Arm with Crossbar, Up To 27" Displays, VESA 75x75/100x100, Max 33lb/15kg, C-Clamp, Fully Articulating, Mechanical Spring, TAA

Product ID: H2M1AS2-MONITOR-ARM



This crossbar monitor desk mount is designed to support up to two 27-inch displays, creating an ergonomic multi-monitor setup that provides an extensive viewing area for productivity. The built-in handle enables moving all monitors simultaneously, while the spring-assisted arm enables multiple adjustments to suit different ergonomic needs.

The mechanical spring arm enables toolless height adjustment of up to 12.9in (32.7cm) with effortless one-touch motion. The maximum arm extension is 22.6in (57.4cm) and a total weigh capacity of 33lb (15kg).

This monitor mount is ideal for bezel-less or slim bezel displays, creating a more extensive and seamless viewing experience that enhances multitasking and productivity. The VESA mounts can slide along the crossbar, allowing for further adjustments.

The monitors' VESA mounts enable support +/-15 swivel, +65/-15 tilt, and 360 screen rotation for portrait/landscape orientation.

To maintain an organized workspace, the arms feature a cable management channel along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup.

Certifications, Reports and Compatibility



Applications

Features

- **DESK MOUNT MONITOR ARM:** Dual monitor mount for up to 27-inch displays; Max 33lb (15kg); VESA plate supports 75x75/100x100mm Patterns; Crossbar keeps monitors perfectly aligned at all times; Articulating mechanical spring arm; TAA-compliant
- **SYNCHRONIZED MOVEMENT:** Crossbar design with built-in handle enables moving the dual monitor setup without realigning the monitors; Monitor stand includes tools to adjust arm tension; Max arm extension 22.6in (57.4cm), height range 7.9-20.8in (20.2-52.9cm)
- **MECHANICAL SPRING ONE-TOUCH ADJUSTMENT:** Full-motion arm features a high-quality mechanical spring for smooth and effortless one-touch motion; Mechanical springs are more robust and resistant to wear over time compared to gas springs; Backed for 10 years
- **DISPLAY ADJUSTMENT:** Ergonomic dual-monitor mount w/toolless adjustments of +/-15 swivel, +65/-15 tilt, & 360 screen rotation (portrait/landscape); The crossbar swivels +/-90, spring arm supports 360 rotation, & swivel arm supports 180 rotation
- **ORGANIZED WORKSPACE:** Cable management channels along the arms of the multi-monitor mount keep cables organized and out of sight, while a cable clip at the base helps maintains a tidy setup; Thumb screws included for tool-less monitor mounting

Hardware

| | |
|----------------------------|---|
| Warranty | 10 Years |
| Wallmountable | No |
| Cable Management | Yes |
| Tools Included | Yes |
| Articulating | Yes |
| # of Displays Supported | 2 |
| Mounting Options | Desk & Grommet Clamp |
| VESA Hole Pattern(s) | 75x75 mm 100x100 mm |
| Mounting Surface Thickness | Desk Clamp: Table Thickness 0.8 - 2.3in (2 - 6cm) |

Performance

| | |
|-------------------------------|-----------------|
| Weight Capacity (Per Display) | 33.1 lb [15 kg] |
| Minimum Display Size | 17" |

| | |
|-------------------------|------------------|
| Maximum Display Size | 27" |
| Fits Curved Display | No |
| Fits UltraWide Displays | No |
| Height Adjustment | Yes |
| Minimum Height | 8.0 in [202 mm] |
| Maximum Height | 20.8 in [529 mm] |
| Minimum Arm Extension | 6.3 in [160 mm] |
| Maximum Arm Extension | 22.6 in [574 mm] |
| Display Tilt | +65 / -15 |
| Display Swivel | +/-15 |
| Swivel / Pivot | +180 / -180 |
| Display Rotation | 360 |
| Anti-theft | No |

Physical Characteristics

| | |
|-----------------------|------------------------------|
| Color | Black |
| Construction Material | Aluminum, Steel, and Plastic |
| Product Length | 25.2 in [64.0 cm] |
| Product Width | 31.2 in [79.3 cm] |
| Product Height | 20.8 in [52.9 cm] |
| Weight of Product | 13.2 lb [6.0 kg] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Length | 13.9 in [35.2 cm] |
| Package Width | 31.5 in [80.0 cm] |
| Package Height | 6.7 in [17.1 cm] |
| Shipping (Package) Weight | 13.8 lb [6.3 kg] |

What's in the Box

| | |
|---------------------|------------------------|
| Included in Package | 1 - Monitor Arm |
| | 1 - Base EVA Cushion |
| | 2 - VESA Monitor Mount |
| | 8 - VESA Screws |
| | 1 - Cable Clip |
| | 1 - M3 Hex Key |
| | 1 - M6 Hex Key |
| | 1 - Crossbar |
| | 2 - Crossbar Endcaps |
| | 4 - M6x12 Screws |
| | 4 - M6 Cap Nuts |
| | 1 - Grab Handle |
| | 1 - Quick-Start Guide |
| | |

****Product appearance and specifications are subject to change without notice.***