



# WRECKER 150mm x 7/11 Tpi - 5 pc

## MULTI MATERIAL: HEAVY DUTY WRECKER™ BLADES

- Strong and precise: Thick 1.27 mm blade body.
- Bi-Metal construction: Excellent blade life and performance.
- Tooth geometry: Aggressive strengthened tooth tip design and uniform gullet depth allows for more material to be removed per stroke for faster cutting.
- Blade shape: Sloped - The sloped shape makes this blade ideal for plunge cutting. Most suited for cutting metal and for demolition applications (wood with nails).



|                                               |                                                                                               |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------|
| Article Number                                | 48475701                                                                                      |
| Blade length (mm)                             | 150                                                                                           |
| Materials suited for                          | Thick metal > 4 mm Medium metal 1.5 - 4 mm Non ferrous metal (Cu/Al) Wood with nails & screws |
| Max. cutting capacity cast iron pipes [mm]    | ø 10 - 100                                                                                    |
| Max. cutting capacity metal pipe              | ø 10 - 100                                                                                    |
| Max. cutting capacity non ferrous metals [mm] | 4 - 10                                                                                        |
| Max. cutting capacity steel (mm)              | 4 - 10                                                                                        |