

Eaton 002220

Catalog Number: 002220

Eaton xEffect Ci Enclosures Switch- & Controlgear Enclosure.
Insulated enclosure, smooth sides, HxWxD=375x375x225mm, NA
type



General specifications

Product Name	Catalog Number
Eaton xEffect Ci Enclosures Switch- & Controlgear Enclosure	002220
	EAN
	4015080022206
Product Length/Depth	Product Height
225 mm	375 mm
Product Width	Product Weight
375 mm	3.475 kg
Compliances	Certifications
IEC/EN62208	UL (Category Control Number NITW)
UL 508A CSA-C22.2 No.94	Specially designed for North America
CE marking	UL508A
RoHS conform	UL (File No. E499317)
	UL listed

Product specifications

Used with

Industrial control panels

Special features

Smooth side plates, without knockouts Sealable cover fasteners
Include fixing straps for wall mounting

Type

Basic enclosure Individual enclosure for North America Individual enclosures with covers xEnergy Safety Ci

Features

UV resistance beneath protective shield
Cover with overpressure release

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility.

10.13 Mechanical function

Meets the product standard's requirements.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Lower part: 960 °C / cover: 850 °C

10.2.4 Resistance to ultra-violet (UV) radiation

Not relevant to indoor installations.

10.2.5 Lifting

20 kg per enclosure with support frame and lifting aid met; assembled and secured as per the latest applicable instruction leaflet.

10.2.6 Mechanical impact

Resources

Brochures

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

Certification reports

[eaton-xeffect-ci-certificate-of-compliance-en-us.pdf](#)

Drawings

[eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-015.eps](#)

[eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-017.eps](#)

[eaton-enclosures-xenergy-safety-ci-lv-systems-dimensions-007.eps](#)

Installation instructions

[05670392.pdf](#)

Installation videos

[xEffect CI stand-alone polycarbonate enclosure](#)

mCAD model

[ci44_200_na.dwg](#)

[ci44_200_na.stp](#)

IK10

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

IP65

10.4 Clearances and creepage distances

Is the panel builder's responsibility.

10.5 Protection against electric shock

Protection class 2, therefore not applicable.

10.6 Incorporation of switching devices and components

Is the panel builder's responsibility.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

$U_i = 1000 \text{ V AC}$

10.9.3 Impulse withstand voltage

8 kV

10.9.4 Testing of enclosures made of insulating material

Meets the product standard's requirements.

Surface finishing

Resistant to corrosion

RAL 7035, light gray (base)

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Creepage resistance

KB160, KC175 (base, to IEC 60112)

KB100, KC200 (cover, to IEC 60112)

Degree of protection

4X (NEMA)

IK10

UL/CSA Types 1, 12, 13, 4X, indoor only

IP65

IP65 (IEC)

Enclosure material

Plastic

Surface protection

Other

Circuit integrity

Other

Base type

RAL 7035, smooth sides

Unit type

Stand-alone device

Built-in depth

200 mm

Heat diss. ambient 35°C delta T:20°C wall mount individ. encl.
top (IEC 60890)

31 W

Heat diss. ambient 35°C delta T: 20°C wall mount middle encl.
top (IEC 60890)

27 W

Heat diss. ambient 35°C delta T:20°C wall mount starting encl.
top (IEC 60890)

29 W

Heat diss. ambient 35°C delta T:35°C wall mount individ. encl.
top (IEC 60890)

62 W

Heat diss. ambient 35°C delta T: 35°C wall mount middle encl.
top (IEC 60890)

53 W

Heat diss. ambient 35°C delta T:35°C wall mount starting encl.
top (IEC 60890)

57 W

Color

Gray

Light gray (RAL 7035, base)

Transparent, smoky gray (cover)

Cover/door color

Transparent

Cover/door model

Closed

Cover/door type

None

Transparent

Optional

Number of openings (flange plates)

0

Plate thickness (cabinet)

9 mm

Plate thickness (cover/door)

6 mm

RAL-number

7035

Surface resistance (IEC 60093)

10 T Ω

Width in number of modular spacings

15

Ambient operating temperature details

-40 °C - 80 °C

Mounting method

Surface mounted (plaster)

Number of rows

0

Dielectric strength

30 kV/mm

Protection class

II

Number of modules

1

Surface treatment

Resistant to corrosion

Internal depth

200 mm

Mounting depth

200 mm

Nominal current

1600 A

Number of conduit inlets

0

Suitable for

Outdoor use

Lightning protection

Saline spray resistance



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)