RN73C1J13K7BTG ✔ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 2-1614350-9

13.7K ohm, Surface Mount Precision Resistor, Thin Film, 0603, .063 W, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RN73

View on TE.com >

Passive Components > Resistors > Surface Mount Resistors



Resistance Value: **13.7K Ω**

Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0603**

Power Rating: **.063 W**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	50 V
Resistance Value	13.7K Ω
Power Rating	.063 W
Resistance Class	1kΩ – 1MΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C

Industry Standards

Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Cut Tape Length

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1-1676142-3
RN 0805 100K 0.01% 10PPM 5K RL




TE Part # 1614349-9
RN 0603 10K 0.1% 10PPM CUT LENGTH



TE Part # 1676153-2
RN 0805 10K 0.1% 10PPM 1KRL




TE Part # 1676153-3
RN 0805 10K 0.1% 10PPM 5KRL




TE Part # 8-1879130-4
RN 0402 5K11 0.1% 10PPM 5K RL

Also in the Series | Holsworthy RN73



Surface Mount Resistors(3641)

Customers Also Bought



TE Part #DT8P-BT-BK
BOOT, 8P, REC, ST, BLK



TE Part #DT8S-BT-BK
BOOT, 8P, PLG, ST, BLK



TE Part #2-31890-1
PIDG R 22-16 COMM 22-18 MIL 8



TE Part #CAT-J41-DDRC
DEUTSCH DT Receptacle Connectors



TE Part #87224-3
03 MODII HDR SRST UNSHRD .100



TE Part #DT06-08SA-E003
PLG, 8P, GRY, N, CAP, A



TE Part #5-1614351-5
RN 0603 20R 0.1% 10PPM 1K RL



TE Part #9-1614882-8
CPF 0603 20R 0.1% 25PPM 1K RL



TE Part #1462042-9
IMC06CGR=IM Relay 140mW 12V 1CO

Documents

Product Drawings

RN 0603 13K7 0.1% 10PPM CUT LENGTH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1614350-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1614350-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1614350-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

High Precision Resistors (SMD) - Type RN73 Series - Tyco Electronics Passives

English