




## TEST PROBE RECEPTACLES



✓ Active

 **PRODUCT DRAWING**  
English

 **3D PDF**



TE CONNECTIVITY (TE)

### TST P REC 130LO BI GRN TPBR

FASTON | [Special Purpose Terminals](#)

1-582118-5

TE Internal Number: 1-582118-5

[Always EU RoHS/ELV Compliant](#)

Height above PC Board **5.84 mm [ .23 in ]**

Funnel Entry **Without**

Contact Mating Area Plating Material **Tin**



#### Product Drawings

##### ASSEMBLY, TEST PROBE

PDF  
English

#### CAD Files

##### Customer View Model

3D\_IGS.ZIP  
English

##### Customer View Model

3D\_STP.ZIP  
English

##### Customer View Model

2D\_DXF.ZIP  
English

##### 3D PDF

PDF  
English

#### Product Specifications

##### Application Specification

##### Test Probe Receptacle Contacts

PDF  
English

[Test Probe Receptacle Contacts](#)

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Funnel Entry	Without
	Product Classification	Connectors - Specialty
	Type of Connector	Test Probe Receptacle
	Product Category	Connectors - Printed Circuit Board
	Applies To	Printed Circuit Board
	Product Type	Connector
Body Features	Receptacle/Leg Material	Brass 6
Contact Features	Contact Mating Area Plating Material	Tin
	Contact Base Material	Beryllium Copper
	Contact Mating Area Plating Material Finish	Bright
Termination Features	Termination Post Length	3.3 mm [ .13 in ]
Mechanical Attachment	Number of Mounting Legs	2
Housing Features	Housing Material	Nylon GF
	Housing Color	Green
Dimensions	Height above PC Board	5.84 mm [ .23 in ]
Product Compliance	<a href="#">Statement of Compliance</a> PDF <a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	



