



RM40

miniature relays



- Very small dimensions
- High switching capacity up to 5 A or 8 A
- Cover with enhanced sealing protects the relay in course of soldering and cleaning
- Applications: for household equipment, office machines, control devices, alarm systems, in industrial control, industrial controllers
- Recognitions, certifications, directives: RoHS,  

Contact data

Number and type of contacts		1 CO	1 NO
Contact material		1 CO: AgNi , AgNi/Au 3 µm	1 NO: AgSnO₂
Rated / max. switching voltage	AC	1 CO: 250 V / 380 V	1 NO: 250 V / 440 V
Min. switching voltage		5 V AgNi, 1 V AgNi/Au 3 µm	5 V AgSnO ₂
Rated load	AC1 DC1	1 CO: 5 A / 250 V AC 1 CO: 5 A / 30 V DC	1 NO: 8 A / 250 V AC 1 NO: 8 A / 30 V DC
Min. switching current		10 mA AgNi, 1 mA AgNi/Au 3 µm	10 mA AgSnO ₂
Rated current		1 CO: 5 A	1 NO: 8 A
Max. breaking capacity	AC1	1 CO: 1 250 VA	1 NO: 2 000 VA
Min. breaking capacity		50 mW AgNi, 1 mW AgNi/Au 3 µm	50 mW AgSnO ₂
Contact resistance		≤ 100 mΩ	

Coil data

Rated voltage	DC	3 ... 48 V
Must release voltage		DC: ≥ 0,05 U _n
Operating range of supply voltage		see Table 1
Rated power consumption	DC	0,20 W

Insulation according to PN-EN 60664-1

Dielectric strength			
• between coil and contacts		4 000 V AC	type of insulation: reinforced
• contact clearance		1 000 V AC	type of clearance: micro-disconnection
Contact - coil distance			
• clearance		≥ 5 mm	
• creepage		≥ 5 mm	

General data

Operating / release time (typical values)		8 ms / 4 ms	
Electrical life (number of cycles)			
• resistive AC1	360 cycles/hour	> 10 ⁵	1 CO: 5 A, 250 V AC 1 NO: 8 A, 250 V AC
• resistive DC1	1 800 cycles/hour	> 10 ⁵	1 CO: 5 A, 30 V DC 1 NO: 8 A, 30 V DC
Mechanical life	18 000 cycles/hour	> 10 ⁷	
Dimensions (L x W x H)		20 x 10 x 10,5 mm	
Weight		6 g	
Ambient temperature	• operating	-40...+85 °C	
Cover protection category		IP 64	PN-EN 60529
Shock resistance		10 g	
Vibration resistance		1,5 mm DA (constant amplitude)	10...55 Hz
Solder bath temperature		max. 235 °C	
Soldering time		max. 3,5 s	


The data in bold type pertain to the standard versions of the relays.

Coil data - DC voltage version


Table 1

Coil code	Rated voltage V DC	Coil resistance at 20 °C Ω	Acceptable resistance	Coil operating range V DC	
				min. (at 20 °C)	max. (at 20 °C)
1003	3	45	$\pm 10\%$	2,25	4,5
1005	5	125	$\pm 10\%$	3,75	7,5
1006	6	180	$\pm 10\%$	4,50	9,0
1009	9	405	$\pm 10\%$	6,75	13,5
1012	12	720	$\pm 10\%$	9,00	18,0
1024	24	2 880	$\pm 10\%$	18,00	36,0
1048	48	11 520	$\pm 10\%$	36,00	72,0

Dimensions




Connection diagrams (pin side view)




Coil temperature rise

Fig. 1



Release time


Fig. 2



RM40

miniature relays


Pinout (solder side view)



Mounting

Relays **RM40** are designed for direct PCB mounting.

Ordering codes



Examples of ordering code:

RM40-2011-85-1003 relay **RM40**, for PCB, one changeover contact, contact material AgNi, for PCB, coil voltage 3 V DC, in cover IP 64

RM40-3021-85-1024 relay **RM40**, for PCB, one normally open contact, contact material AgSnO₂, coil voltage 24 V DC, in cover IP 64

PRECAUTIONS:

1. Ensure that the parameters of the product described in its specification provide a safety margin for the appropriate operation of the device or system and never use the product in circumstances which exceed the parameters of the product. 2. Never touch any live parts of the device. 3. Ensure that the product has been connected correctly. An incorrect connection may cause malfunction, excessive heating or risk of fire. 4. In case of any risk of any serious material loss or death or injuries of humans or animals, the devices or systems shall be designed so to equip them with double safety system to guarantee their reliable operation.