




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 1022 – 2583 CMA

Stud Size: #8, M4

Features

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	2
-----------------	---

Body Features

Product Weight	.442 g
----------------	--------

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	None



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.1 in
Wire Size	1022 – 2583 CMA
Stud Diameter	4.2 mm[.165 in]
Tongue Thickness	.76 mm[.03 in]
Product Length	11.68 mm[.46 in]
Barrel Inside Diameter	1.9 mm, 2.79 mm[.075 in][.11 in]
Compatible Insulation Diameter (Max)	3.43 mm[.135 in]
Compatible Insulation Diameter Range	2.5 – 3.4 mm[.1 – .135 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	15000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 150070-5
RING



TE Part # 7-2150461-7
OCEAN_2.0_SPARE_PART_KIT-120F155F




TE Part # 2150461-1
OCEAN_2.0_Applicator-E-120F155F-REM




TE Part # 2150461-2
OCEAN_2.0_Applicator-E-120F155F-REA

Customers Also Bought




TE Part #282080-1
AMP SUPERSEAL 1.5 SERIES 2P PL



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #794896-3
2 CIR MINI UMNL RND WIRE HOLES



TE Part #282403-1
MINI MIC SRS REC CONT

Documents

Product Drawings
RING TONGUE I.S.
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_160434-2_H_c-160434-2-h.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_160434-2_H_c-160434-2-h.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160434-2_H_c-160434-2-h.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English

Product Specification

English

Agency Approvals

UL Report

English