


Cable label, self laminating, white/transparent, thermal transfer print, 19.05x25.40mm, H2=57.10mm, 2500pcs.

Art.-No. 596-09896 | TAG9TD3-896-CL/WH | 




- High-quality self-laminating labels
- Suitable for marking of wires and cables
- Laminating function gives excellent protection against humidity and mechanical abrasion
-
-



More products in this product group:

[Self-laminating labels "Ladder Style", thermal transfer >](#)

Application	The specially formulated adhesive labels give the highest quality print clarity when printed on thermal transfer printers. The range of materials and ribbons have been developed to suit the needs of most users. Designing and printing labels is simple and users can quickly print out professional labels in a matter of moments when using TagPrint Pro labelling software.
Chem. Material Properties	flame retardant, resistant to oils, water and wide range of solvents.
Colour	White (WH), Transparent (CL)
Colour Marking Field	White (WH)
Material	Type 896, Vinyl (896)
Mech. material properties	permanent adhesive
PART DESCRIPTION	TAG9TD3-896-CL/WH
Pack Content	2500 pcs.
Package Content packed in	pcs.
Product Family	Helatag 896
Product Group	Self-laminating labels "Ladder Style", thermal transfer
Self adhesive (Yes/No)	Yes
Type	TAG9TD3
Variant	Roller form



Bundle ø max.	12.10 mm
Bundle ø min.	5.50 mm
HR	25.40 mm
Height (H)	19.05 mm
Height (H2)	57.10 mm
Print Method	thermal transfer print
Thickness (T)	75 µm
Thickness of Foil	80
Thickness of foil test method	ASTM D3652-83
VR	63.50 mm
Width (W)	25.40 mm
Width of Liner (WL)	82.00 mm

Adhesive	Acrylic
Curing Temperature	from +10 °C
ELV compliant (Article 4 - 2)	YES
Halogen-free	No
Hazardous Goods	No
Initial tack	110 g/cm ²
Initial tack	ASTM D2979-71
Operating Temperature	-40 °C to +80 °C
Peel strength	550 N/m
Peel strength test method	PSTC 7
Pre-Printed	No
ROHS compliant	Yes
Recommended Ribbon Type	TT932DOUT
Shear strength	120 h
Shear strength test method	FINAT FTM 8
Shelf Life	Minimum 1 year upon receipt / maximal 2 years after production date.
Specifications	RoHS ✓
UL Recognized (US)	Yes



GTIN-13 / EAN	4031026209920
Labels per Row	3 pcs.
Packaging 1 - Height (m)	0.15 m
Packaging 1 - Length (m)	0.165 m
Packaging 1 - Qty	2500
Packaging 1 - Type	bag
Packaging 1 - Volume (m³)	0.0022275 m³
Packaging 1 - Weight (kg)	0.797501 kg
Packaging 1 - Width (m)	0.09 m
Packaging 3 - Height (m)	0.24 m
Packaging 3 - Length (m)	0.55 m
Packaging 3 - Qty	30000
Packaging 3 - Type	carton
Packaging 3 - Volume (m³)	0.0515 m³
Packaging 3 - Weight (kg)	10.07 kg
Packaging 3 - Width (m)	0.39 m
Packaging 4 - Length (m)	1.2 m
Packaging 4 - Type	pallet
Packaging 4 - Width (m)	0.8 m
Storage Temperature	+21 °C
Storage conditions	50% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness.

More Information

UNSPSC Key	55121612
------------	----------

