



Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (3.7% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # CAT-076-BNCJKISG50 BNC RF Connector: Jack Assembly, Isolated Ground Protection, 50 Ohm	 TE Part # CAT-076-BNCVTBAY BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism	 TE Part # CAT-076-BNCJKRA75C BNC RF Connector: Jack, Right-angle, 75 Ohm	 TE Part # CAT-076-BNCRABAY BNC Right Angle M Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism
 TE Part # CAT-076-BNCJKSH50 BNC RF Connector: jack assembly - short, 50 Ohm, 4Ghz	 TE Part # 1-1337494-0 BNC R/A Shld PCB Skt 50Ohm Nickel Pltd	 TE Part # 5-1634516-1 BNC RM BHJ Hex 50Ohm Nickel Pltd RG58C/U	 TE Part # 5-1634503-1 BNC Str PCB Skt 50Ohm Nickel Pltd
 TE Part # 5-1634503-3 BNC Str PCB Skt 75Ohm Nickel Pltd	 TE Part # 5-1634556-0 BNC LP ELBOW B/HEAD PCB SKT 50 OHMS 6.15	 TE Part # 5413779-3 COML BNC,50 OHM, HEX CRIMP	 TE Part # 5222132-1 JACK,VERTICAL,PCB,75 OHM,BNC
 TE Part # 5413476-2 JACK,DECOUPLER,PCB,VERT,BNC	 TE Part # 6274315-1 BNC JACK, NONSWITCHING	 TE Part # 1-1337541-0 BNC Ins Str PCB Skt 500hm White	 TE Part # 1-1634505-0 BNC Ins Str PCB Skt 500hm Black
 TE Part # 1-1634622-0 BNC Ins R/A PCB Skt 750hm Black	 TE Part # 5-1634506-1 BNC Str PCB Skt 50Ohm Nickel Pltd 19.8	 TE Part # 5-1634511-2 BNC Str Jk Hex 50Ohm Nickel Pltd RG58C/U	 TE Part # 5-1634513-1 BNC LOW PROFILE ELBOW SOCKET 50 OHMS

Customers Also Bought





TE Part #5748536-1
KIT,RCPT,9P,HDP-20,SHLD HDWRE



TE Part #5499923-9
A/L UNIV HDR 40P VERT LG LAT



TE Part #5748526-1
KIT,PLUG,9P,HDP-20,SHLD HDWRE



TE Part #5745967-4
25 RCPT SP/FMS STD



TE Part #5747871-4
09 PLUG SP/FMS STD



TE Part #7-51863-1
PIDG R 22-16 COMM 22-18 MIL 6



TE Part #3-747580-1
SHLDNG FERRULE, PLTD, BULK PKG



TE Part #5747150-4
09 RCPT SP/FMS STD



TE Part #5747299-4
15 RCPT SP/FMS STD



TE Part #748627-2
SHLD JACKSCREW,PLTD

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-221128-0_AH.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-221128-0_AH.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-221128-0_AH.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

COAXICON 50-Ohm BNC RF Series Commercial Plug (Hex Crimp) Connector

English

