

Analogue universal time switches - tactic 171.1

Item No 01.80.0002.1 / EAN Code 4010940003982



PRODUCT DESCRIPTION

APPLICATIONS

- ▶ Machinery control
- ▶ Heating systems control

Weight

155 g

Dimension

72 x 72 x 55 mm (H x B x T)

TECHNICAL DATA**Electrical Data**

Supply voltage	AC 220-240 V \pm 10% 50 Hz
Current output	Changeover, potential free
Current capacity - ohmic load	16 A / 250 V AC
	21 A / 250 V AC (UL)
Current capacity - inductive load cos. ϕ 0.6	8 A / 250 V AC
Switching capacity - minimal	100 mA / 20 V AC/DC
Load incandescent bulb	1.300 W
Power consumption	1 VA
Accuracy	Mains synchronised
Power reserve	no

Power connection

Device	Flat connection DIN 6.3
--------	-------------------------

Operating specifications

Manual switch	Automatic mode
	Fix ON/OFF
Channels	1
Tempering protection	Lead-sealable
Program	Weekly program (ON/OFF)

Display and format

Shortest switching time	ON/OFF 2 Hours
-------------------------	----------------

Operating conditions

Temperature (operation)	-20° C ... +55° C
-------------------------	-------------------

General specifications

Drive type Synchronous

Colour Gray

Analogue universal time switches - tactic - tactic 171.1

GRÄSSLIN
by INTERMATIC

39,5 mm (T) mounting depth

###

Compliance with standards

Protection class II, according to corresponding mounting

Approval mark CE

Standards and guidelines EN 60730-1

EN 60730-2-7


Scope of delivery

Housing Glass

Terminal cover

Base

DIMENSIONAL DRAWINGS



CIRCUIT DIAGRAMS

