



## Pullers, three-armed

11351

Product no. 71035101  
GTIN 4018754342051  
Model 11351/1

**Label.** Puller Clamping w.160mm x Clamping d.130mm

### Properties.

- three-armed
- with self-centring puller arms
- for gears, ball bearings, pulleys and similar parts from a shaft or axle
- double-sided use of the extractor hooks: narrow arm end (20 mm) for narrow installation spaces, wide arm end (24 mm) with slot (8 mm) for pulling off washers or gear wheels with the aid of 8 mm screws
- nitrided spindle, no lubrication required, maintenance-free
- zinc plated

### Benefits.

For quick and reliable removal of gears, ball bearings, pulleys and for extracting the outer rings of ball bearings and bushings from drilled holes.

Automatic pressure of the arms under load makes application easier.

The nitrided surface of the spindle allows it to move easily so it does not require additional lubrication.

The arm ends have a narrow and wide design and can therefore be used on both sides.

Outstanding flexural strength thanks to legs with precisely manufactured profiles and smooth, milled guides.

## Product highlights.



### **Reliable sliding properties.**

The high-quality tempered and specially coated pressure spindle has particularly good sliding properties in the thread, is maintenance-free and does not require oiling.



### **Adapted access geometry.**

Heavy-duty puller hooks made of oil-hardened Chrome Alloy Steel with special access geometry for tight spaces. Custom radii for shafts and axes.



### **Protection against damage.**


The centering tip is freely rotating - to protect the shafts from damage.

**For increased safety.**

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.



**Technical drawing.**



**Technical attributes.**

<b>External hex drive (mm)</b>	19 mm
<b>Thickness of hook base tip mm (a)</b>	3 mm
<b>Hook base width mm (b)</b>	24 mm
<b>Hook foot depth mm (c)</b>	12 mm
<b>Size</b>	1
<b>Number of hooks</b>	3
<b>max. load</b>	7,5 t
<b>Clamping depth (h) mm</b>	130 mm
<b>Spindle thread size</b>	M18 x 1,5 x 170
<b>Span mm (w)</b>	160 mm

**Logistics data.**

<b>Depth mm (IFS)</b>	215
<b>Width mm (IFS)</b>	160
<b>Height mm (IFS)</b>	140
<b>WEEE/ElektroG</b>	nicht ear-pflichtig
<b>Length (packaged, mm)</b>	225
<b>Width (packaged, mm)</b>	175
<b>Height (packaging, mm)</b>	153
<b>Volume (packaged, dm3)</b>	6.024375 dm3
<b>Product no.</b>	71035101
<b>Weight (gross, kg)</b>	2,574
<b>Weight PAP (kg)</b>	0,178
<b>Weight PVC (kg)</b>	0,000
<b>GTIN</b>	4018754342051
<b>Country of origin AWR</b>	GERMANY
<b>Region of origin</b>	Nordrhein-Westfalen
<b>Customs tariff no.</b>	82055980
<b>Packing standard</b>	1

Weight (g)

2600 g

## Variants.

Product no.	Model No. (ERP)	Description	GTIN
71035101	11351/1	Puller Clamping w.160mm x Clamping d.130mm	4018754342051
71035102	11351/2	Puller Clamping w.220mm x Clamping d.170mm	4018754342068

## GTIN.



## Spare part(s), spare part(s) for.



79281006  
Puller spindle

## Images.





**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

[info@stahlwille.de](mailto:info@stahlwille.de) · [www.stahlwille.com](http://www.stahlwille.com)

© STAHLWILLE Eduard Wille GmbH, Wuppertal