



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Shielded: **No**

Number of Positions: **25**

Sealable: **No**

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
Sealable	No

Configuration Features

Number of Positions	25
---------------------	----

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Operation/Application

Shielded	No
----------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JUNE 2024 (241)


Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #214346-E  
SMCB 26 F AB VV 6-01 VH \* 0008 137 E002




TE Part #214348-E  
SMCB 68 F AB VV 6-01 VH \* 0008 137 E002




TE Part #3838513001  
44A0121-26-0/9




TE Part #1658612-2  
25 POS HDF RCPT, MS, LEAD FREE




TE Part #747275-2  
025 LP HDF STRAIN RELIEF



TE Part #214347-E  
SMCB 50 F AB VV 6-01 VH \* 0008 137 E002




TE Part #825433-3  
MOD 2 PINHDR 1X3 P.



TE Part #160773-6  
PL LOOSE PIECE REC 0.5-1.5 MM2 PTPBR



TE Part #133183-E  
[MJ HS V \\* 8 8 \\* \\* \\* \\* \\* 30 \\* J 3 133819](#)



TE Part #1857211-1  
[KIT, SCREW RETAINER AMPLIMITE,](#)

Documents

Product Drawings

[V42254A4000D 25=SUB D BUEGEL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1393560-6\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1393560-6\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1393560-6\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.