

Technical data

2306S

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	30 mm
D - External diameter	72 mm
B - Bearing/Inner ring width	27 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,5 kg

PRODUCT PERFORMANCE

C - Dynamic load	32000000 mN
C0 - Static load	8750000 mN
Cu - Fatigue limit load	380000 mN
e - Coefficient	0.44
Y0 - Static axial load coefficient	1.5
Y1 - Lower axial load coefficient	1.4
Y2 - Upper axial load coefficient	2.2
N lim - Oil lubrication limit speed	60000 °/s
N lim - Grease lubrication limit speed	48000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	36,5 mm
Da max - Max shoulder diameter OR	65,5 mm



2306S
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm