

**HTSB-1**

HEXAGONAL THREADED SPACER, BRASS

Part No.	Thread "D1" + "D2"		"L" mm	"H" mm	"P1" mm	"P2" mm
HTSB-M2-L-4-1	M2	M2	5.0 / 8.0 / 10.0 / 12.0 / 15.0	4.0	thru	
HTSB-M2-L-4-1	M2	M2	18.0 / 20.0 / 25.0 / 30.0	4.0	8.0	8.0
HTSB-M2.5-L-5-1	M2.5	M2.5	5.0 / 8.0 / 10.0 / 12.0 / 15.0	5.0	thru	
HTSB-M2.5-L-5-1	M2.5	M2.5	18.0 / 20.0 / 25.0 / 30.0	5.0	8.0	8.0
HTSB-M3-L-5-1	M3	M3	5.0 / 8.0 / 10.0 / 12.0 / 15.0 / 18.0 / 20.0	5.0	thru	
HTSB-M3-L-5-1	M3	M3	25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0	5.0	10.0	10.0
HTSB-M3-L-5.5-1	M3	M3	5.0 / 8.0 / 10.0 / 12.0 / 15.0 / 18.0 / 20.0	5.5	thru	
HTSB-M3-L-5.5-1	M3	M3	25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0	5.5	10.0	10.0
HTSB-M4-L-7-1	M4	M4	5.0 / 8.0 / 10.0 / 12.0 / 15.0 / 18.0 / 20.0	7.0	thru	
HTSB-M4-L-7-1	M4	M4	25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0 / 70.0	7.0	10.0	10.0
HTSB-M5-L-8-1	M5	M5	5.0 / 8.0 / 10.0 / 12.0 / 15.0 / 18.0 / 20.0	8.0	thru	
HTSB-M5-L-8-1	M5	M5	25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0 / 70.0	8.0	10.0	10.0

Material: Brass CuZn39Pb3
 Plating: G3 E nickel to DIN 267
 Max. Torque: 430 N / mm²
 Tolerance: ± 0,1 mm
 Std. Pk.: 100 pcs.

Note:

HTSB	M5	L	10	1
Part	Thread	Length	SW	Type