

Datasheet

RS PRO External HDPE Float Switch

Stock No.s: 1919492, 1919493



| MS SERIES



* = protective earth wire not included on "C" (C/O) versions.

The MS series of cable end float switches are designed for controlling levels in large tanks, cisterns or reservoirs and can be directly installed on submersible pumps. The casing is manufactured in blow moulded Polyethylene (HDPE), with 5m PVC cable with protective earth conductor as standard*. The switching element is a microswitch, with UL, VDE and CENELEC approvals, activated by a moving stainless steel ball and having an electrical life of 200,000 operations. Non-hygroscopic closed-cell expanded polyurethane is injected around the switch housing within the outer casing, hermetically sealing the unit. It is capable of working down to 100 metres depth in water.

The "U" version with polyurethane cable is for use in fuel oils.

Features


- Direct power switching
- Cable mounting
- 100 metre depth capability




Technical

	RS Stock No.	Contact Form	Switching Current Max. (Amps)			Power Rating Max.		Switching Voltage Max.		Cable Matl.	Cable Length	Body Matl.	Temp. Range		Max. Pressure
R			AC												
			Resistive	Inductive	DC	AC (VA)	DC (W)	AC	DC	Width.	*	mut.	°C	°F	11000010
19	919492	N/0	10	4	1	750	24	250	24	PVC	5m	HDPE	0-45	32-113	10 bar
19	919493	N/C	10	4	1	750	24	250	24	PVC	5m	HDPE	0-45	32-113	10 bar

INSTALLATION






Wiring Detail

Contact Form	Contact Type	Wires			
A	Normally open	Brown/ Black			
В	Normally closed	Brown/ Blue			
r	Changeover	Brown/ Black	Normally Open		
	Glialigeovel	Brown/ Blue	Normally Closed		

Note. "Normally" means "No Liquid Present"



All dimensions are in millimeters.



MS RS Pro 2022