


AC3218



AS-Interface control cabinet module

SmartL25 4 AO (C) C IP20



Application

Application	Installation in control cabinets
-------------	----------------------------------

Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	157
Reverse polarity protection		yes
Additional voltage supply	[V]	20...30 DC; (AUX)
Additional voltage supply		optional
Max. current consumption from additional supply	[mA]	550; (AUX)

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 4
------------------------------	-------------------------------

Outputs

Number of analogue outputs	4; (connection of 2-wire or 4-wire actuators)	
Analogue current output	[mA]	0...20
Max. load	[Ω]	600
Max. voltage drop across load for nominal current	[V]	10
Overload protection		yes

AC3218



AS-Interface control cabinet module

SmartL25 4 AO (C) C IP20

Resolution of analogue output	16 (1 bit = 1 μ A)
Actuator supply outputs	AS-i / AUX

Operating conditions

Ambient temperature [°C]	0...70
Storage temperature [°C]	-25...75
Max. relative air humidity [%]	90; (non condensing)
Max. height above sea level [m]	2000
Protection	IP 20
Protection rating terminals	IP 20
Pollution degree	2

Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-4	
UL approval	power supply	Class 2

AS-i classification

AS-i version	2.11; 3.0
AS-i addressing	addressing socket
Extended addressing mode	no
AS-i master profile	M3; M4
AS-i profile	S-7.3.6
AS-i I/O configuration [hex]	7
AS-i ID code [hex]	3.6

Mechanical data

Weight [g]	202.1
Housing	housing for DIN rail mounting
Type of mounting	mounting on DIN rail
Dimensions [mm]	126 x 25.4 x 108
Materials	PC-GF20

Displays / operating elements

Display	analogue signal	LED, yellow channels AO1...AO4
	diagnosis	LED, yellow
	operation	LED, green AS-i, AUX
	errors	LED, red

Accessories

Items supplied	COMBICON connectors
----------------	---------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

AC3218



AS-Interface control cabinet module

SmartL25 4 AO (C) C IP20

Electrical connection

pin headers: 4 x ; Spacing: 5.0 mm

Connection

O+	C1	O-	0V
O+	C2	O-	0V
O+	C3	O-	0V

0V	O-	C4	O+
A+	A-	E+	E-

O+	actuator supply +24V
C1...4	analogue output Current
O-	actuator supply 0V
0V	analogue output 0V
A+	AS-i +
A-	AS-i -
E+	external actuator supply +24V
E-	external actuator supply 0V