

SIEMENS

Product data sheet

6ES7355-2SH00-0AE0


SIMATIC S7-300,
TEMPERATURE CONTROL MODULE FM 355 S,
4 CHANNELS, STEP AND PULSE,
4 AI + 8 DI + 8 DO INCL. MULTI-LANG CONFIG.
PACK.,
MANUAL AND GETTING STARTED (GER/EN/IT) ON
CD-ROM

General information

Consisting of MLFB

SWR:6ES73552CH000AE0_01;
SWR:6ES73552CH000AE0_02;
SWR:6ES73552CH000AE0_03;
SWR:6ES73552CH000AE0_04;
SWR:6ES73552CH000AE0_05;
SWR:6ES73552CH000AE0_06

Supply voltage

Load voltage L+

Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Input current

from load voltage L+ (without load), max.	270 mA ; typ. 220 mA
from backplane bus 5 V DC, max.	75 mA ; typ. 50 mA

Power losses

Power loss, typ.	5.5 W
------------------	-------

Power loss, max.	6.9 W
Digital inputs	
Number/binary inputs	8
Input characteristic curve acc. to IEC 61131, Type 2	Yes
Input voltage	
Rated value, DC	24 V
for signal "0"	-3 to +5 V
for signal "1"	13 to 30 V
Input current	
for signal "1", typ.	7 mA
Cable length	
Cable length, shielded, max.	1000 m
Cable length unshielded, max.	600 m
Digital outputs	
Number/binary outputs	8
Functionality/short-circuit strength	Yes ; Electronic
Limitation of inductive shutdown voltage to	L+ (-1.5 V)
Lamp load, max.	5 W
Controlling a digital input	Yes
Load resistance range	
lower limit	240 Ω
upper limit	4 k Ω
Output voltage	
for signal "1", min.	L+ (-2.5 V)
Output current	
for signal "1" rated value	0.1 A
for signal "1" permissible range for 0 to 60 °C, min.	5 mA
for signal "1" permissible range for 0 to 60 °C, max.	150 mA
for signal "0" residual current, max.	0.5 mA
Parallel switching of 2 outputs	
for logic links	Yes
Switching frequency	
with resistive load, max.	100 Hz

with inductive load, max.	0.5 Hz
on lamp load, max.	100 Hz
Aggregate current of outputs (per group)	
all mounting positions	
up to 60 °C, max.	400 mA
Cable length	
Cable length, shielded, max.	1000 m
Cable length unshielded, max.	600 m
Analog inputs	
Number of analog inputs	4
permissible input voltage for voltage input (destruction limit), max.	20 V
permissible input current for current input (destruction limit), max.	40 mA
Input ranges	
Voltage	Yes
Current	Yes
Thermocouple	Yes
Resistance thermometer	Yes
Input ranges (rated values), voltages	
0 to +10 V	Yes
Input resistance (0 to 10 V)	100 k Ω
-1.75 to +11.75 V	Yes
Input resistance (-1.75 to +11.75 V)	100 k Ω
Input ranges (rated values), currents	
0 to 20 mA	Yes
Input resistance (0 to 20 mA)	50 Ω
0 to 23.5 mA	Yes
Input resistance (0 to 23.5 mA)	50 Ω
-3.5 to +23.5 mA	Yes
Input resistance (-3.5 to +23.5 mA)	50 Ω
4 to 20 mA	Yes
Input resistance (4 to 20 mA)	50 Ω
Input ranges (rated values), thermoelements	

Type B	Yes
Input resistance (Type B)	10 MΩ
Type E	Yes
Input resistance (Type E)	10 MΩ
Type J	Yes
Input resistance (type J)	10 MΩ
Type K	Yes
Input resistance (Type K)	10 MΩ
Type R	Yes
Input resistance (Type R)	10 MΩ
Type S	Yes
Input resistance (Type S)	10 MΩ
Input ranges (rated values), resistance thermometers	
Pt 100	Yes
Input resistance (Pt 100)	10 MΩ
Thermocouple (TC)	
for thermocouples	Type B, E, J, K, R, S
[nicht versorgt: TAK_ABT261_001_000]	
internal temperature compensation	Yes
external temperature compensation with Pt100	Yes
Resistance thermometer (RTD)	
Characteristic linearization	
for resistance thermometer	Pt100 (standard)
Characteristic linearization	
Parameterizable	Yes
Cable length	
Cable length, shielded, max.	200 m ; 50 m at 80 mV and thermocouples
Analog value creation	
Measurement principle	integrating
Integrations and conversion time/ resolution per channel	
Resolution with overrange (bit including sign), max.	14 bit
Conversion time (per channel)	100 ms ; At 50/60 Hz
Settling time	

for resistive load	0.1 ms
for capacitive load	3.3 ms
for inductive load	0.5 ms
Encoder	
Connection of signal encoders	
for voltage measurement	Yes
for current measurement as 4-wire transducer	Yes
Connectable encoders	
2-wire sensor	Yes
Permissible quiescent current (2-wire sensor), max.	1.5 mA
Errors/accuracies	
Linearity error (relative to input area)	+/- 0,05 %
Temperature error (relative to input area)	+/- 0,005 %/K
Operational limit in overall temperature range	
Voltage, relative to input area	+/- 0,06 % ; +/-0.06 to +/-0.7%
Current, relative to input area	+/- 0,06 % ; +/-0.06 to +/-0.7%
Resistance-type thermometer, relative to input area	+/- 0,06 % ; +/-0.06 to +/-0.7%
Basic error limit (operational limit at 25 °C)	
Voltage, relative to input area	+/- 0,04 % ; +/-0.04 to +/-0.5%
Current, relative to input area	+/- 0,04 % ; +/-0.04 to +/-0.5%
Resistance-type thermometer, relative to input area	+/- 0,04 % ; +/-0.04 to +/-0.5%
Interference voltage suppression for $f = n \times (f_l \pm 1\%)$, f_l = interference frequency	
Series mode interference (peak value of interference < rated value of input range), min.	40 dB
common mode voltage (USS < 2.5 V) , min.	70 dB
Interrupts/diagnostics/status information	
Substitute values connectable	Yes ; Parameterizable
Control technology	
Number of closed-loop controllers	4
Galvanic isolation	
Galvanic isolation controller	

between the channels	No
between the channels and the backplane bus	Yes ; Optocoupler
Permissible potential difference	
between inputs and MANA (UCM)	2.5 V DC
between M internally and the inputs	75 VDC / 60 VAC
Isolation	
Isolation checked with	500 V DC
Connection method	
required front connector	2x 20-pin
Dimensions	
Width	80 mm
Height	125 mm
Depth	120 mm
Weight	
Weight, approx.	470 g
Status	Apr 9, 2012